

The tables below indicate the weighing capacity and the minimum display for each unit, depending on the balance model.

Unit	Capacity			Minimum display
	FZ-120 <i>i</i> WP FX-120 <i>i</i> WP	FZ-200 <i>i</i> WP FX-200 <i>i</i> WP	FZ-300 <i>i</i> WP FX-300 <i>i</i> WP	
Gram	122	220	320	0.001
Ounce (Avoir)	4.30	7.76	11.2	0.00005
Pound	0.268	0.485	0.705	0.000005
Pound/Ounce	0L 4.30oz	0L 7.76oz	0L 11.29oz	1L 0.01oz
Troy Ounce	3.92	7.07	10.2	0.00005
Metric Carat	610	1100	1600	0.005
Momme	32.5	58.6	85.3	0.0005
Pennyweight	78.4	141	205	0.001
Grain (UK)	1882	3395	4938	0.02
Tael (HK general, Singapore)	3.22	5.82	8.46	0.00005
Tael (HK jewelry)	3.25	5.87	8.54	0.00005
Tael (Taiwan)	3.25	5.86	8.53	0.00005
Tael (China)	3.90	7.04	10.2	0.00005
Tola (India)	10.4	18.8	27.4	0.0001
Messghal	26.0	46.9	68.2	0.0005

Unit	Capacity			Minimum display
	FZ-1200 <i>i</i> WP FX-1200 <i>i</i> WP	FZ-2000 <i>i</i> WP FX-2000 <i>i</i> WP	FZ-3000 <i>i</i> WP FX-3000 <i>i</i> WP	
Gram	1220	2200	3200	0.01
Ounce (Avoir)	43.0	77.6	112	0.0005
Pound	2.68	4.85	7.05	0.00005
Pound/Ounce	2L 11.03oz	4L 13.60oz	7L 0.88oz	1L 0.01oz
Troy Ounce	39.2	70.7	102	0.0005
Metric Carat	6100	11000	16000	0.05
Momme	325	586	853	0.005
Pennyweight	784	1414	2057	0.01
Grain (UK)	18827	33951	49383	0.2
Tael (HK general, Singapore)	32.2	58.2	84.6	0.0005
Tael (HK jewelry)	32.5	58.7	85.4	0.0005
Tael (Taiwan)	32.5	58.6	85.3	0.0005
Tael (China)	39.0	70.4	102	0.0005
Tola (India)	104	188	274	0.001
Messghal	260	469	682	0.005