






CERTIFIED: PORTABLE CRIMP TOOLS

Tooling-to-Terminal Cross Reference

OPEN BARREL TERMINALS		Style	Wire Range		Max		Hand Tools Premium	Tool Type Premium
			AWG	mm ²	Insul.	Dia.		
AMPLIMITE D-Sub. Connectors		Size 20 DF Contacts	28-24	0.08-0.2	.040	1.02	91503-1	SAHT
			24-20	0.2-0.5	.060	1.52		
AMPMODU Connectors		Size 22 DF Contacts	28-22	0.08-0.3	.040	1.02	91520-1	SAHT
		Mod. IV Contacts	26-22	0.12-0.3	.061	1.55	91517-1	SAHT
		Locking Clip Contacts	24-20	0.2-0.5	.069	1.75	91516-1	SAHT
			26-22	0.12-0.3	.062	1.58	91533-1	SAHT
		MTE & Tandem Spring Contacts	32-28	0.03-0.08	.054	1.37	1901786-1	SAHT
		Short Point Contacts	26-22	0.12-0.3	.065	1.65	91531-1	SAHT
			32-22	0.03-0.3	.060	1.52	91518-1	SAHT
CPC Connectors, M Series Connectors		Type II Contacts	28-24	0.08-0.2	.055	1.40	91538-1	SAHT
			24-20	0.2-0.6	.062	1.57	91538-1	SAHT
			18-16	0.8-1.4	—	—	91538-1	SAHT
			14	2	—	—	91539-1	SAHT
		Type III+ Contacts	30-26	0.05-0.15	.060	1.52	91515-1	SAHT
			26-24	0.12-0.2	.055	1.40	91515-1	SAHT
			24-20	0.2-0.6	.080	2.03	91515-1	SAHT
			24-20	0.2-0.6	.100	2.54	91523-1	SAHT
			24-20	0.2-0.6	.120	3.05	91542-1	SAHT
			18-16	0.8-1.25	.100	2.54	91505-1	SAHT
		Type XII Contacts	18-14	0.8-2	.100	2.54	91519-1	SAHT
			16	1.25	.160	4.06	90382-2	HHHT
			14-12	2-3	.160	4.06	90382-2	HHHT
			10-8	5-7	.220	5.59	90384-1	HHHT
FASTON Straight Receptacles (Premier Line Only)		250 Series	22-18	0.3-0.8	.130	3.30	90166-1	DAHT
			18-14	0.8-2	.170	4.32	90165-1	DAHT
			14-10	2-5	.200	5.08	90120	DAHT
MATE-N-LOK Connectors		Commercial Contacts	30-22	0.05-0.3	.075	1.91	91515-1	SAHT
			24-18	0.2-0.8	.100	2.54	91512-1	SAHT
			20-14	0.5-2	.130	3.30	91504-1	SAHT
			24-18	0.2-0.8	.100	2.54	91510-1	SAHT
		Universal & Universal II Contacts	20-14	0.5-2	.130	3.30	91500-1	SAHT
			20-18	0.5-0.8	.200	5.08	91508-1	SAHT
			16-14	1.25-2	.200	5.08	91506-1	SAHT
		Mini-Universal	20-16	0.5-1.25	.126	3.20	91536-1	SAHT
		Mini-Universal II Contacts	26-22	0.12-0.3	.069	1.75	91529-1	SAHT
			22-18	0.3-0.8	.094	2.39	91522-1	SAHT
20-16	0.5-1.25		.126	3.20	91594-1	SAHT		