



CoolSplice | CoolSplice Connectors

TE Internal #: 2213600-1  
Splices, Butt Splice, 12 – 14 AWG / 14 – 16 AWG Wire Size, 4 – 2.5 mm<sup>2</sup> / 2.5 – 1.5 mm<sup>2</sup> Wire Size, Sealable, Splice Capacity 2, CoolSplice Connectors  
[View on TE.com >](#)

Terminals & Splices > Splices > CoolSplice Quick Connect Splice



Wire Size: 2.5 – 1.5 mm<sup>2</sup>, 4 – 2.5 mm<sup>2</sup>  
Sealable: **Yes**  
Splice Capacity: 2  
Splice Features: **End Feed**

[All CoolSplice Quick Connect Splice \(12\)](#)

Features

Product Type Features

Sealable	Yes
Splice Type	Butt Splice
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Splice Capacity	2
Compatible With Wire & Cable Type	Discrete Wire

Electrical Characteristics

Current Rating	15 A
Operating Voltage	600 VAC

Body Features

Button Color	Blue, Yellow
Splice Features	End Feed