

1 Laboratory Equipment

2 Measuring Equipment

3 Laboratory Furniture

4 Life Science and Analysis

5 Bottles and Containers

6 Laboratory Related Tools and Fixtures

7 Cleaning and Sterilization

8 Safety Protection Supplies

9 Clean Environment Equipment

A Balances

B Thermometers and Hygrometers

C Data-Loggers and Recorders

D Water and Soil Analysis

E Air and Gas Analysis

F Natural Environment Analysis

G Electrical Measuring Equipment

H Physical Property Measuring Equipment

I Microscopes

J Fiber Scopes and Loupes

K Lasers / Optical Equipment

L Measuring Tools

## Stand Magnifiers

### MAGNIFIER LIGHT (Table Stand Type) JP

Order No.	2-3090 (Without Dimming Function)			2-3091 (With Dimming Function)		
	Magnification Ratio	Model No.	JPY	Model No.	JPY	Ref.No
-11	2x	SKKL-B Model 2x	¥ 29,500	ENVL-B Model 2x	¥ 40,500	067170
-12	4x	SKKL-B Model 4x	¥ 42,000	ENVL-B Model 4x	¥ 53,000	067170
-13	6x	SKKL-B Model 6x	¥ 60,000	ENVL-B Model 6x	¥ 65,000	067170
-14	8x	SKKL-B Model 8x	¥ 75,000	ENVL-B Model 8x	¥ 78,000	067170
-15	10x	SKKL-B Model 10x	¥ 91,000	ENVL-B Model 10x	¥ 94,000	067170
-16	2x	LEKs-B Wide Model 2x	¥ 55,000	LEK-B Wide Model 2x	¥ 67,000	067170

#### ■ Feature

- Provided with round lens made of optical glass in pursuit of usability. ● Available in wide model which uses wide lens with approx.15% larger dia. suitable for inspection requiring wide field.
- Equipped with circular LED for light source allowing you to conduct inspection under uniform irradiation.

#### ■ Specification

- Lens Dia. : 2x · 4x / φ130mm, 6x / φ105mm, 8x · 10x / φ90mm, Wide 2x / φ150mm
- Lens Constitution : 2x · Wide 2x / 1sheet, 4x · 6x / 2sheets Pair, 8x / 3sheets Pair, 10x / 4sheets Pair ● Power Supply : AC100~240V 50/60Hz (If 125V or higher voltage is required, plug must be changed.) ● Power Cord : 1.8m ● Light Source : LED (design life : 40000 hours)

### MAGNIFIER LED LIGHT (Light Box Type) JP

Order No.	Model No.	Magnification Ratio	JPY	Ref.No
2-3092-16	LEK-CL Wide Model 2x	2x	¥ 160,000	067170

#### ■ Feature

- Uses wide lens with dia. of φ150mm allowing wide field inspection.
- Provided with white LED light as light source for two kinds of illumination such as epi-illumination and transmission illumination.
- Equipped with separately controllable upper and lower lights.
- Comes with dimming function.

#### ■ Specification

- Lens Dia. : φ150mm ● Lens Constitution : 1sheet
- Power Supply : AC100~240V 50/60Hz (If 125V or higher voltage is required, plug must be changed.)
- Power Cord : 1.8m ● Light Source : LED (design life : 40000 hours)

### MAGNIFIER LIGHT (Free Arm · Clamp Type) JP

Order No.	2-3094 (Without Dimming Function)			2-3095 (With Dimming Function)		
	Magnification Ratio	Model No.	JPY	Model No.	JPY	Ref.No
-11	2x	SKKL-F Model 2x	¥ 35,500	ENVL-F Model 2x	¥ 48,500	067170
-12	4x	SKKL-F Model 4x	¥ 47,000	ENVL-F Model 4x	¥ 61,000	067170
-13	6x	SKKL-F Model 6x	¥ 66,000	ENVL-F Model 6x	¥ 73,000	067170
-14	8x	SKKL-F Model 8x	¥ 81,000	ENVL-F Model 8x	¥ 85,000	067170
-15	10x	SKKL-F Model 10x	¥ 96,000	ENVL-F Model 10x	¥ 102,000	067170
-16	2x	LEKs-F Wide Model 2x	¥ 61,000	LEK-F Wide Model 2x	¥ 75,000	067170

#### ■ Feature

- Equipped with function to freely set location of lens so that it can be used in any environment.
- Equipped with white LED for light source allowing you to conduct inspection under uniform irradiation.

#### ■ Specification

- Lens Dia. : 2x · 4x / φ130mm, 6x / φ105mm, 8x · 10x / φ90mm, Wide 2x / φ150mm
- Lens Constitution : 2x · Wide 2x / 1sheet, 4x · 6x / 2sheets Pair, 8x / 3sheets Pair, 10x / 4sheets Pair
- Power Supply : AC100~240V 50/60Hz (If 125V or higher voltage is required, the plug must be changed.)
- Power Code Length : 1.8m ● Light Source : LED (design life : 40000 hours)
- Arm Length : 1m ● Clamping Width : 15~60mm

### MAGNIFIER LAMP (Illuminated magnifying glass) CN

Order No.	Model No.	Dimensions (mm)	JPY	Ref.No
1-9472-01	RUMI Rupe	238~450x135x118~355	¥ 5,000	067150
1-9472-11	Replacement 12W Fluorescent Tube	φ123x13	¥ 1,000	067150

#### ■ Feature

- Equipped with 2 types of lens and hands-free movable arm, enhances work efficiency.
- The built-in inverter eliminates flicker, and mitigates fatigue of eyes.

#### ■ Specification

- Magnification : 2x · 4.25x
- Lens Dimensions : approx. φ85mm ● Power Supply : AC100V 50/60Hz
- Power Consumption : 9.1/9.2W (50/60Hz)
- Fluorescent Tube : 12W (Lamp life approx. 4000hours)
- Weight : 940 g ● Power Cord Length : 1.45m



B Wide Type

B type



CL Wide Type



SKKL-F type

ENVL-F type

### REPLACEMENT LENS (For Lighting Magnifier · SYSTEM LENS) JP

Order No.	Model No.	Magnification	Lens Dia. (φmm)	Lens Constitution	JPY	Ref.No
2-3096-01	2	2x	130	1sheet Lens	¥ 13,000	067170
2-3096-02	4	4x	105	2sheets	¥ 27,000	067170
2-3096-03	6	6x		Pair Lens	¥ 41,000	067170
2-3096-04	8	8x	90	4sheets	¥ 59,000	067170
2-3096-05	10	10x		Pair Lens	¥ 74,000	067170

- Feature ● Possible to used for light magnifying glass · B · CL · F type (excluding wide type).

