

AXEL

2-759-01 Precision Pressure Regulator SRS-HS-GHN3-2 GHN3-2



Order No. 2-759-01
Model No. GHN3-2
JAN Code 0000000000000


JPY:
29,600

Standard price **USD:**
197.81

Exchange rate 1USD= 149.64JPY

Valid price in Japan

Quantity 1unit



Calibration Available

Features

- Clean washed and assembled pressure regulator for analytical standard gas and physical and chemical science devices.
- Provided with 2-steps depressurization system realizing stable gas supply as outlet pressure is stable even if primary side pressure significantly fluctuates.

Spec

- Primary pressure: 15.0MPa or less
- Adjustment pressure: 0.1 - 0.6MPa
- Side pressure gauge (inlet/outlet): 25/1.0MPa
- Applicable gas: O₂ · N₂ · Ar · Air
- Decompression structure: 1 stages
- Maximum flow rate: 100L/min
- Inlet: W22 14 mountains right cap nut
- Outlet: Rc1/4 valve
- Body material: Brass
- SRS-HS
- Model number: GHN3-2

► Package size : 180×150×180 mm 1.58 kg

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	816
AS ONE Catalog 2021 [Instruments for Laboratory]	761
AS ONE Catalog 2019 [Instruments for Laboratory]	739