

AXEL

T&D Corporation

61-8493-87 Voltage Recorder TR-55i-V



Order No.	61-8493-87
Model No.	TR-55i-V
JAN Code	4589413190219
	JPY: 19,000
	USD: 126.85
Standard price	
	Exchange rate 1USD= 149.78JPY
	Valid price in Japan
Quantity	1piece

Features

- Data logger for measuring and recording voltage.
- It is battery-powered and can be installed anywhere.
- Recorded data can be transferred to a personal computer via either the communication port TR-50U2 (sold separately) or the data collector TR-57DCi (sold separately) for graph display and data analysis.
- Data collectors allow on-site data collection and browsing without the need to collect data loggers.

Spec

- Measurement target: Voltage 1ch
- Measurement range: 0 - 22V
- Accuracy: $\pm 0.5\text{mV} \pm 0.3\%$ of read value
- Display: Measured value, Battery remaining amount, Other
- Recording data: 16000
- Recording interval: 15 ways:
- Recording mode: endless/onetime
- Communication: Optical communication, Infrared communication
- How to check the Alarm: Body liquid crystal screen, Body LED
- Power supply: Lithium battery
- Main unit operation environment: Temperature/-40 - 80°C
- Size: H62mm x W47mm x D19mm
- Waterproof: IP64
- Battery life: Approx 16 months
- Accessories: Input module, Cell, Other

» Package size : 90×80×40 mm

Product Catalog

Catalog Name	Page
AS ONE Catalog 2021 [Instruments for Laboratory]	745