

# AXEL

## 1-6666-06 Pressure Regulator GF2-2510LNVPV GF2-2510-LN-VPV



|                |   |
|----------------|---|
| Order No.      | 1-6666-06   |
| Model No.      | GF2-2510-LN-VPV                                       |
| JAN Code       | 0000000000000   |
| Standard price | <b>JPY:</b><br><b>54,400</b>                          |
|                | <b>USD:</b><br><b>363.54</b>                          |
|                | Exchange rate 1USD= 149.64JPY<br>Valid price in Japan |
| Quantity       | 1piece  |

### Features

- Type of cleaning and assembly of developed for special gas standard gas analyst equipment.
- 2-steps type is 2-steps pressure-reducing, so outlet pressure is stable.
- Flowmeter type can be precise flow rate setting and supply continuously.
- Purge valve type can eliminate outside air mixed at the time of cylinder connection.

### Spec

- Side pressure meter: Input / 25 MPa, Output / 1 MPa
- Fittings: inlet / W 22 left bag nut, outlet / φ6 mm hose opening or Rc 1/4 (PT 1/4 female screw)
- pressure of use: Entrance / 14.8 MPa (MAX MAX MAX MAX MAX), Exit / 0.6 MPa (MAX MAX MAX MAX MAX)
- Material: Main / brass, Valve Sheet / Teflon R or Daifuron, Diaphragm / Nitrile Gom Teflon (R)
- flow rate: 25 L/min
- Weight: 2.1 kg
- Model number: GF2-2510-LN-VPV
- Type: Two-stage type with cartridge mounting outlet purge valve
- Corresponding gas: H2
- GF Series

▶ Package size : 215×215×180 mm 2.37 kg

### Product Catalog

| Catalog Name                                     | Page |
|--|------|
| AS ONE Catalog 2023 [Instruments for Laboratory] | 815  |
| AS ONE Catalog 2021 [Instruments for Laboratory] | 760  |
| AS ONE Catalog 2019 [Instruments for Laboratory] | 738  |
| AS ONE Catalog 2017 [Instruments for Laboratory] | 573  |
| AS ONE Catalog 2015 [Instruments for Laboratory] | 545  |