

# AXEL

## 1-6666-07 Pressure Regulator GF2-2506LNF30 GF2-2506-LN-F30



Order No.	1-6666-07
Model No.	GF2-2506-LN-F30
JAN Code	0000000000000
	<b>JPY:</b> <b>61,600</b>
	<b>USD:</b> <b>411.66</b>
Standard price	
	Exchange rate 1USD= 149.64JPY
	Valid price in Japan
Quantity	1piece

### Features

- Type of cleaning and assembly of developed for special gas standard gas analyst equipment.
- 2-steps type is 2-steps pressure-reducing, so outlet pressure is stable.
- Flowmeter type can be precise flow rate setting and supply continuously.
- Purge valve type can eliminate outside air mixed at the time of cylinder connection.

### Spec

- Side pressure meter: Input / 25 MPa Output / 0.6 MPa
- Fittings: Indoor / W 22 Left bag nut, Exit / φ6 mm hose port or M12-P 1.0 male screw
- pressure of use: Entrance / 14.8 MPa (MAX MAX MAX MAX MAX), Exit / 0.4 MPa (MAX MAX MAX MAX MAX)
- Material: Main / brass, Valve Sheet / Teflon R or Daifuron, Diaphragm / Nitrile Gom Teflon (R)
- flow rate: 30 L/min
- Weight: 2.3 kg
- Model number: GF2-2506-LN-F 30
- Type: Two-stage type with a flow rate meter mounted on the cylinder
- Corresponding gas: H2
- GF Series

▶ Package size : 208×179×222 mm 1.8 kg

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	815
AS ONE Catalog 2021 [Instruments for Laboratory]	760
AS ONE Catalog 2019 [Instruments for Laboratory]	738
AS ONE Catalog 2017 [Instruments for Laboratory]	573
AS ONE Catalog 2015 [Instruments for Laboratory]	545