

AXEL

2-5169-13 Pressure Regulator GF2-2510-RN-VPVO GF2-2510-RN-VPVO



Order No.	2-5169-13
Model No.	GF2-2510-RN-VPVO
JAN Code	0000000000000
	JPY: 54,400
	USD: 363.54
Standard price	
	Exchange rate 1USD= 149.64JPY
	Valid price in Japan
Quantity	1piece

Features

- Type of cleaning and assembly of developed for special gas standard gas analyst equipment.
- 2-steps type is 2-steps pressure-reducing, so outlet pressure is stable.
- Flowmeter type can be precise flow rate setting and supply continuously.
- Purge valve type can eliminate outside air mixed at the time of cylinder connection.

Spec

- Side pressure meter: Input / 25 MPa Output / 1.0 MPa
- Fittings: inlet / W 22 right bag nut, exit / φ6 mm hose opening or Rc 1/4 (PT 1/4 female screw)
- pressure of use: Entrance / 14.8 MPa (MAX MAX MAX MAX MAX), Exit / 0.6 MPa (MAX MAX MAX MAX MAX)
- Material: Main / brass, Valve Sheet / Teflon R or Daifuron, Diaphragm / Nitrile Gom Teflon (R)
- flow rate: 25 L/min
- Weight: 2.1 kg
- Model number: GF2-2510-RN-VPV
- Type: A two-stage type with an outlet and purge valve
- Corresponding gas: O₂
- GF Series

▶ Package size : 205×205×175 mm 2.36 kg

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	815
AS ONE Catalog 2021 [Instruments for Laboratory]	760
AS ONE Catalog 2019 [Instruments for Laboratory]	738
AS ONE Catalog 2017 [Instruments for Laboratory]	573
AS ONE Catalog 2015 [Instruments for Laboratory]	545