

AXEL

AS ONE Corporation

1-5455-02 Digital Thermometer IT-2000



Order No.	1-5455-02
Model No.	IT-2000
JAN Code	4562108502412
	JPY: 18,800
	USD: 125.64
Standard price	
	Exchange rate 1USD= 149.64JPY
	Valid price in Japan
Quantity	1unit

Calibration Available

Features

- Data hold function to temporarily fix data.
- Max. temperature at the time of measuring can be automatically memorized and recalled after measuring.
- Shockproof at the time of falling and Holster case protecting body from dust are standard equipment.

Spec

- Model number: IT-2000
- Measurement range: -50 to +1300°C
- Resolution (°C): 0.1/1 (selected by the switch)
- Sensor type: K class thermocouple
- Measurement accuracy: $\pm(0.3\% + 1^\circ\text{C}) / <1000^\circ\text{C}$, $\pm(0.5\% + 1^\circ\text{C}) / >1000^\circ\text{C}$
- Temperature factor (23 \pm 5°C): 0.15 x (measurement accuracy)
- Sampling rate: 2.5 times/second
- Display: 4 digits LCD display, Maximum 9999 display
- Used temperature and humidity: 0 - 50°C, 0 - 80%RH (0 - 35°C), 0 - 60% (35 - 50°C)
- Storage temperature: -20 to +60°C
- Input protection: 60V, DC/24Vrms
- Power supply: 006P (9V) battery x 1 (optional)
- External dimensions: Body only/64 x 160 x 26mm, With holster case/74 x 170 x 39mm
- Weight: Approximately 300g (body)
- Accessories: Holster case
- *Sensor probe is not included in the package.

» Package size : 175×90×50 mm 430 g

Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	553