

# AXEL

Hanna Instruments

## 1-3226-11 All Concentration Range Reagent HI 93735-0 for Total Hardness Meter HI93735-0



Order No.	1-3226-11
Model No.	HI93735-0
JAN Code	4580304567318
	<b>JPY:</b> <b>30,000</b>
	<b>USD:</b> <b>200.48</b>
Standard price	
	Exchange rate 1USD= 149.64JPY Valid price in Japan
Quantity	1set

Calibration Available

### Features

- Possible to measure water hardness in 0~750ppm.

### Spec

- Model number: HI 93735-0
- Daily waterproof type
- All concentration range reagent (3 concentration range x 100 times each)
- Measurement range (mg/L): 0 - 750

▫ Package size : 380×255×260 mm 120 g

### Product Catalog

Catalog Name	Page
AS ONE Catalog 2023 [Instruments for Laboratory]	701
AS ONE Catalog 2021 [Instruments for Laboratory]	661
AS ONE Catalog 2019 [Instruments for Laboratory]	634
AS ONE Catalog 2017 [Instruments for Laboratory]	499
AS ONE Catalog 2015 [Instruments for Laboratory]	463
PROCESS SOLUTION Catalog 2016 [For Facilitating Quality Control]	221
Bio Lab Catalog 2014 [Supplies & Reagent for Life Science Research]	158