



レギュレーサ (偏心)

単位: mm

Sch40		Sch80		端面から 端面まで の距離 H	概略重量 (kg) (1段落の場合)					径の呼び	
内径 I D	厚さ T	内径 I D	厚さ T		Sch5S	Sch10S	Sch20S	Sch40	Sch80	A	B
16.1	2.8	14.3	3.7	—	—	—	—	—	—	15	1/2
21.4	2.9	19.4	3.9	38.1	0.036	0.045	0.052	0.059	0.076	20	3/4
27.2	3.4	25.0	4.5	50.8	0.060	0.099	0.105	0.117	0.149	25	1
35.5	3.6	32.9	4.9	50.8	0.077	0.126	0.134	0.158	0.207	32	1 1/4
41.2	3.7	38.4	5.1	63.5	0.115	0.190	0.202	0.246	0.327	40	1 1/2
52.7	3.9	49.5	5.5	76.2	0.166	0.275	0.339	0.375	0.512	50	2
65.9	5.2	62.3	7.0	88.9	0.308	0.435	0.503	0.728	0.952	65	2 1/2
78.1	5.5	73.9	7.6	88.9	0.375	0.530	0.697	0.940	1.26	80	3
90.1	5.7	85.4	8.1	101.6	0.496	0.701	0.925	1.29	1.79	90	3 1/2
102.3	6.0	97.1	8.6	101.6	0.563	0.797	1.05	1.55	2.16	100	4
126.6	6.6	120.8	9.5	127.0	1.10	1.33	1.93	2.52	3.53	125	5
151.0	7.1	143.2	11.0	139.7	1.46	1.76	2.57	3.59	5.42	150	6
199.9	8.2	190.9	12.7	152.4	2.00	2.84	4.55	5.68	8.59	200	8
248.8	9.3	237.2	15.1	177.8	3.59	4.21	6.78	9.58	15.2	250	10
297.9	10.3	283.7	17.4	203.2	5.85	6.57	9.43	14.7	24.3	300	12

◎ 概略重量は基準寸法による計算値であり、ステンレス鋼(SUS304)の比重 7.93g/cm³ を使用しています。