


ハンドリーマ Hand Reamer



公差 (Tolerance)	D				d		
	0.01トビ Increment 0.01	+0.005 0	0.5~3 +0.007 +0.002	3.1~6 +0.009 +0.004		6.1~10 +0.012 +0.006	-0.02 -0.05
	10.1~18 +0.015 +0.007	18.1~30 +0.017 +0.008	31~50 +0.02 +0.009	51~ +0.024 +0.011			
0.005トビ Increment 0.005		0.505~0.905 +0.005 0	0.955~ +0.003 0				

右刃ストレート 食付角度1° SKH51
Straight Flute Chamfer Angle1° HSS

直径 (φD)	食付長 (T)	刃長 (ℓ)	全長 (L)	シャンク径 (φd)	刃数 (N)	セクタ
Dia.	Chamfer Length	Length of Flutes	Overall Length	Shank Dia.	Number of Flutes	Center
0.5	2.5	12	30	2	4	60°凸
0.6	2.5	12	30	2	4	60°凸
0.7	2.5	12	30	2	4	60°凸
0.8	3	15	35	2	4	60°凸
0.9	4	20	40	2	4	60°凸
1	4	20	40	2	4	60°凸
1.1	5	25	45	2	4	60°凸
1.2	5	25	45	2	4	60°凸
1.3	5	25	50	3	4	60°凸
1.4	5	25	50	3	4	60°凸
1.5	5	25	50	3	4	60°凸
1.6	6	30	55	3	4	60°凸
1.7	6	30	55	3	4	60°凸
1.8	6	30	55	3	4	60°凸
1.9	6	30	60	3	4	60°凸
2	6	30	60	3	4	60°凸
2.1	6	30	60	3	4	60°凸
2.2	6	30	60	3	4	60°凸
2.3	7	35	65	3	4	60°凸
2.4	7	35	65	3	4	60°凸
2.5	7	35	65	3	4	60°凸
2.6	7	35	65	3	4	60°凸
2.7	7	35	65	3	4	60°凸
2.8	7	35	65	3	4	60°凸
2.9	8	40	72	3	6	60°凹
3	8	40	72	3	6	60°凹
3.1	8	40	72	3.1	6	60°凹
3.2	8	40	75	3.2	6	60°凹
3.3	8	40	75	3.3	6	60°凹
3.4	8	40	75	3.4	6	60°凹
3.5	8	40	75	3.5	6	60°凹
3.6	8	40	75	3.6	6	60°凹
3.7	8	40	80	3.7	6	60°凹
3.8	8	40	80	3.8	6	60°凹
3.9	8	40	80	3.9	6	60°凹
4	8	40	80	4	6	60°凹
4.1	8	40	80	4.1	6	60°凹
4.2	9	45	85	4.2	6	60°凹
4.3	9	45	85	4.3	6	60°凹
4.4	9	45	85	4.4	6	60°凹
4.5	9	45	85	4.5	6	60°凹
4.6	9	45	85	4.6	6	60°凹
4.7	9	45	90	4.7	6	60°凹

直径 (φD)	食付長 (T)	刃長 (ℓ)	全長 (L)	シャンク径 (φd)	刃数 (N)	セクタ
Dia.	Chamfer Length	Length of Flutes	Overall Length	Shank Dia.	Number of Flutes	Center
4.8	9	45	90	4.8	6	60°凹
4.9	9	45	90	4.9	6	60°凹
5	9	45	90	5	6	60°凹
5.1	9	45	90	5.1	6	60°凹
5.2	10	45	95	5.2	6	60°凹
5.3	10	45	95	5.3	6	60°凹
5.4	10	45	95	5.4	6	60°凹
5.5	10	45	95	5.5	6	60°凹
5.6	10	45	95	5.6	6	60°凹
5.7	10	50	100	5.7	6	60°凹
5.8	10	50	100	5.8	6	60°凹
5.9	10	50	100	5.9	6	60°凹
6	10	50	100	6	6	60°凹
6.1	10	50	100	6.1	6	60°凹
6.2	10	50	100	6.2	6	60°凹
6.3	10	50	100	6.3	6	60°凹
6.4	10	50	100	6.4	6	60°凹
6.5	10	50	100	6.5	6	60°凹
6.6	10	50	100	6.6	6	60°凹
6.7	11	55	105	6.7	6	60°凹
6.8	11	55	105	6.8	6	60°凹
6.9	11	55	105	6.9	6	60°凹
7	11	55	105	7	6	60°凹
7.1	11	55	105	7.1	6	60°凹
7.2	11	55	110	7.2	6	60°凹
7.3	11	55	110	7.3	6	60°凹
7.4	11	55	110	7.4	6	60°凹
7.5	11	55	110	7.5	6	60°凹
7.6	11	55	110	7.6	6	60°凹
7.7	12	60	115	7.7	6	60°凹
7.8	12	60	115	7.8	6	60°凹
7.9	12	60	115	7.9	6	60°凹
8	12	60	115	8	6	60°凹
8.1	12	60	115	8.1	6	60°凹
8.2	12	60	120	8.2	6	60°凹
8.3	12	60	120	8.3	6	60°凹
8.4	12	60	120	8.4	6	60°凹
8.5	12	60	120	8.5	6	60°凹
8.6	12	60	120	8.6	6	60°凹
8.7	13	65	125	8.7	6	60°凹
8.8	13	65	125	8.8	6	60°凹
8.9	13	65	125	8.9	6	60°凹
9	13	65	125	9	6	60°凹