



EPIC® H-B 24 TSH-RO

Housing design H-B. The industry standard.



Info

- Non-slip ridges for comfortable disconnecting
- More interior space for wiring

EPIC® H-B 24 TG

Housing design H-B. The industry standard.



Info

- Non-slip ridges for comfortable disconnecting

EPIC® H-B 24 TG 2X

Housing design H-B. The industry standard.



Info

- Non-slip ridges for comfortable disconnecting
- For easy introduction of two cables

Benefits

- Ideal for many applications due to a wide range of housings and inserts

Application range

- Plant engineering
- Light & sound technology
- Plastics industry

Product features

EPIC® H-B 24 TSH-RO

- Hood, high version
- Reels for single lever
- Side cable entry
- Versions with / without neck

EPIC® H-B 24 TG

- Hood, low version
- Bolts for double lever
- Straight cable entry
- Versions with / without neck

EPIC® H-B 24 TG 2X

- Hood, low version
- Bolts for double lever
- 2 straight cable entries
- Versions with neck

Suitable inserts

- Refer to Selection Table A 10 to select the required inserts and housings

Technical data

ETIM ETIM 5.0 Class-ID: EC000437
ETIM 5.0 Class-Description: Housing for industrial connectors

Material
Housing: powder-coated aluminium alloy, grey
Lever: zinc-plated steel
Sealing: NBR

IP **Protection rating**
IP 65 (latched)

DIN VDE Certified production control:
VDE-REG. no.: B437
UL-tested:
UL File Number: E75770

Temperature range
-40°C to +100°C,
short-term up to +125°C

Article number	Article description	M	PG	Neck	Pieces / PU
H-B housing: hood (side cable entry, bolts for single lever, high version)					
70154400	H-B 24 TSH-RO 21		21	yes	5
70154600	H-B 24 TSH-RO 29		29	yes	5
79154400	H-B 24 TSH-RO M25	25			5
79154600	H-B 24 TSH-RO M32	32			5
79154800	H-B 24 TSH-RO M40	40			5
H-B housing: hood (straight cable entry, bolts for double lever)					
10121000	H-B 24 TG 21		21	yes	5
10111000	H-B 24 TG 29		29	yes	5
19121000	H-B 24 TG M25	25			5
19111000	H-B 24 TG M32	32			5
H-B housing: hood (2 straight cable entries, bolts for double lever)					
44422019	H-B 24 TG 2XM25	2 x 25		yes	5
44422020	H-B 24 TG 2XM32	2 x 32		yes	5

Photographs are not to scale and do not represent detailed images of the respective products.

Accessories

- SKINTOP® MS-M
- SKINTOP® for industrial connectors
- Easy to install