



EPIC® Protective cover H-A 3



EPIC® Protective cover H-A



EPIC® Protective cover H-B



Technical data

ETIM 5.0 Class-ID: EC002314
ETIM 5.0 Class-Description:
Cap for industrial connectors

Product features

EPIC® Protective cover H-A 3

- Protective cover made of thermoplastics and metal for H-A 3 housings
- Retaining cord with cable lug for attachment with screw on mounting base or wall
- Retaining cord with variable loop for attachment to the cable

EPIC® Protective cover H-A

- Retaining cord with cable lug for attachment with screw on mounting base or wall
- Retaining cord with variable loop for attachment to the cable
- Protective cover made of thermoplastics for H-A 10, H-A 16, H-A 32, H-A 48 housings

EPIC® Protective cover H-B

- Retaining cord with cable lug for attachment with screw on mounting base or wall
- Retaining cord with variable loop for attachment to the cable
- Protective cover made of thermoplastics for H-B 6, H-B 10, H-B 16, H-B 24, H-B 32 housings

| Article number | Article description | Version | Bolts | Securing cord | Clamp | Material | Pieces / PU |
|---|----------------------|---------------------------------------|-------|----------------|-----------------|----------|-------------|
| For H-A 3 panel-mount base, surface-mount base, cable coupler hood with male or female inserts | | | | | | | |
| 10513000 | H-A 3 MDBF-S | for housing H-A 3 with male inserts | 2 | with cable lug | | Metal | 10 |
| 10513100 | H-A 3 MDBF-B | for housing H-A 3 with female inserts | 2 | with cable lug | | Metal | 10 |
| For H-A 3 panel-mount base, surface-mount base, cable coupler hood with male inserts | | | | | | | |
| 10430000 | H-A 3 KDB-S | for housing H-A 3 with male inserts | 2 | | | Plastic | 10 |
| 10430400 | H-A 3 KDBF-S | for housing H-A 3 with male inserts | 2 | with cable lug | | Plastic | 10 |
| For H-A 3 panel-mount base, surface-mount base, cable coupler hood with female inserts | | | | | | | |
| 10430300 | H-A 3 KDB-B | for housing H-A 3 with female inserts | 2 | | | Plastic | 10 |
| 10430100 | H-A 3 KDBF-B | for housing H-A 3 with female inserts | 2 | with cable lug | | Plastic | 10 |
| with bolts for H-A 10-32 panel-mount base, surface-mount base, cable coupler hood | | | | | | | |
| 10457700 | H-A 10 KDB | for housing H-A 10 | 2 | | | Plastic | 5 |
| 10469700 | H-A 16 KDB | for housing H-A 16 | 2 | | | Plastic | 5 |
| 10481700 | H-A 32 KDB | for housing H-A 32 | 4 | | | Plastic | 5 |
| 10457500 | H-A 10 KDBF | for housing H-A 10 | 2 | with cable lug | | Plastic | 5 |
| 10469500 | H-A 16 KDBF | for housing H-A 16 | 2 | with cable lug | | Plastic | 5 |
| 10481500 | H-A 32 KDBF | for housing H-A 32 | 4 | with cable lug | | Plastic | 10 |
| with lever for H-A 10-32 hoods | | | | | | | |
| 10457800 | H-A 10 KDT | for H-A 10 hood | | | 2 snap-in hooks | Plastic | 5 |
| 10469800 | H-A 16 KDT | for H-A 16 hood | | | 2 snap-in hooks | Plastic | 5 |
| 10481800 | H-A 32 KDT | for H-A 32 hood | | | 4 snap-in hooks | Plastic | 5 |
| 10457600 | H-A 10 KDTF | for H-A 10 hood | | with loop | 2 snap-in hooks | Plastic | 5 |
| 10469600 | H-A 16 KDTF | for H-A 16 hood | | with loop | 2 snap-in hooks | Plastic | 5 |
| 10481600 | H-A 32 KDT | for H-A 32 hood | | with loop | 4 snap-in hooks | Plastic | 10 |
| with bolts for H-B 6-24 panel-mount base, surface-mount base, cable coupler hood | | | | | | | |
| 10015000 | H-B 6 KDB | for housing H-B 6 | 2 | with cable lug | | Plastic | 10 |
| 10047000 | H-B 10 KDB | for housing H-B 10 | 4 | with cable lug | | Plastic | 10 |
| 10087000 | H-B 16 KDB | for housing H-B 16 | 4 | with cable lug | | Plastic | 5 |
| 10118000 | H-B 24 KDB | for housing H-B 24 | 4 | with cable lug | | Plastic | 5 |
| with lever for H-B 6-24 hood with bolts | | | | | | | |
| 10016500 | H-B 6 KDT | for H-B 6 hood | | with loop | 2 snap-in hooks | Plastic | 10 |
| 10048500 | H-B 10 KDT | for H-B 10 hood | | with loop | 4 snap-in hooks | Plastic | 10 |
| 10088500 | H-B 16 KDT | for H-B 16 hood | | with loop | 4 snap-in hooks | Plastic | 5 |
| 10119500 | H-B 24 KDT | for H-B 24 hood | | with loop | 4 snap-in hooks | Plastic | 5 |
| with bolts for H-B 6-24 hoods with levers | | | | | | | |
| 10015100 | H-B 6 KDBP | for H-B 6 hood | 2 | with loop | | Plastic | 10 |
| 10047100 | H-B 10 KDBP | for H-B 10 hood | 4 | with loop | | Plastic | 10 |
| 10087100 | H-B 16 KDBP | for H-B 16 hood | 4 | with loop | | Plastic | 10 |
| 10118100 | H-B 24 KDBP | for H-B 24 hood | 4 | with loop | | Plastic | 5 |
| with bolts for H-B 10-32 panel-mount base, surface-mount base, cable coupler hood | | | | | | | |
| 10048700 | H-B 10 KDBF | for housing H-B 10 | 2 | with loop | | Plastic | 10 |
| 10088700 | H-B 16 KDBF | for housing H-B 16 | 2 | with loop | | Plastic | 10 |
| 10118700 | H-B 24 KDBF | for housing H-B 24 | 2 | with loop | | Plastic | 10 |
| 10118020 | H-B 32 / H-A 48 KDBF | for housing H-B 32/H-A 48 | 4 | with loop | | Plastic | 10 |
| with lever for H-B 10-24 hood with bolts | | | | | | | |
| 10048600 | H-B 10 KDTF | for H-B 10 hood | | with loop | 2 snap-in hooks | Plastic | 10 |
| 10088600 | H-B 16 KDTF | for H-B 16 hood | | with loop | 2 snap-in hooks | Plastic | 10 |
| 10118600 | H-B 24 KDTF | for H-B 24 hood | | with loop | 2 snap-in hooks | Plastic | 10 |

Photographs are not to scale and do not represent detailed images of the respective products.