





EPIC® POWER LS1 D6

Circular connectors for servomotors and power supply



EPIC® POWER LS1 D6 (short)

Circular connectors for servomotors and power supply



Info

- Reduced length for cables which are easy to assemble

Suitable contacts:

- EPIC® POWER LS1 Contacts female Page 687
- PU = 5 pieces: the contacts are included. 2 mm contact crimp range is 0.5 - 2.5 mm².
- PU = 20 pieces: the contacts must be ordered separately

Benefits

- High power at smallest installation space, Optimal solution for electric motors
- EMC-optimised design
- Safety use in field environment by high protection class

Application range

- Plant engineering
- Servo drives and servo assemblies

Technical data

	ETIM 5.0 Class-ID: EC001322 ETIM 5.0 Class-Description: Round socket/plug for high currents		Number of contacts 3+PE+4(2mm/1mm) 5+PE(2mm)
	Rated voltage (V) 630 V (2 mm contacts) 250 V (1 mm contacts)		Termination methods Crimp termination: 0.5 - 4.0 mm² (2 mm contacts) Crimp termination: 0.14 - 1.0 mm² (1 mm contacts)
	Rated impulse voltage 6 kV (2 mm contacts) 4 kV (1 mm contacts)		Material Housing: nickel-plated zinc die-casting, nickel-plated brass Insert: PA, Seal: FPM
	Rated current (A) 26A/3+PE+4, 25A/5+PE (2mm contacts) 7 A (1 mm contacts)		Protection rating IP68 (10h / 1m)
	Degree of soiling 3		Cycle of mechanical operation 500
	Contact resistance < 4 mOhm		VDE-tested Certified production control: VDE-REG. no. B25
	Contacts Gold-plated brass		Temperature range -25°C up to +125°C

Article number	Article description	Contacts included	Clamping range in mm	Pin configuration	Pieces / PU
Type LS1 D6, cable connector, 6-pin, for female contacts					
73000004	LS1 D6	6	8.5 - 11	5+PE	5
73000006	LS1 D6		8.5 - 11	5+PE	20
73000005	LS1 D6	6	10.5 - 15.5	5+PE	5
73000007	LS1 D6		10.5 - 15.5	5+PE	20
76123000	LS1 D6	6	7.5 - 15.5	5+PE	5
76123510	LS1 D6		7.5 - 15.5	5+PE	20
44420091	LS1 D6 with 2mm contact for 4mm² termination	6	14 - 17	5+PE	5
44420090	LS1 D6		14 - 17	5+PE	20
Type LS1 D6, cable connector, 8-pin, for female contacts					
73000000	LS1 D6	8	8.5 - 11	3+PE+4	5
73000002	LS1 D6		8.5 - 11	3+PE+4	20
73000001	LS1 D6	8	10.5 - 15.5	3+PE+4	5
73000003	LS1 D6		10.5 - 15.5	3+PE+4	20
76124000	LS1 D6	8	7.5 - 15.5	3+PE+4	5
76124510	LS1 D6		7.5 - 15.5	3+PE+4	20
44420089	LS1 D6 with 2mm contact for 4mm² termination	8	14 - 17	3+PE+4	5
44420088	LS1 D6		14 - 17	3+PE+4	20
Type LS1 D6 short, cable connector, 6-pin, for female contacts					
73000028	LS1 D6	6	8.5 - 11	5+PE	5
73000030	LS1 D6		8.5 - 11	5+PE	20
73000029	LS1 D6	6	10.5 - 15.5	5+PE	5
73000031	LS1 D6		10.5 - 15.5	5+PE	20
76123100	LS1 D6	6	7.5 - 15.5	5+PE	5
76123610	LS1 D6		7.5 - 15.5	5+PE	20
Type LS1 D6 short, cable connector, 8-pin, for female contacts					
73000024	LS1 D6	8	8.5 - 11	3+PE+4	5
73000026	LS1 D6		8.5 - 11	3+PE+4	20
73000025	LS1 D6	8	10.5 - 15.5	3+PE+4	5
73000027	LS1 D6		10.5 - 15.5	3+PE+4	20
76124100	LS1 D6	8	7.5 - 15.5	3+PE+4	5
76124610	LS1 D6		7.5 - 15.5	3+PE+4	20

Photographs are not to scale and do not represent detailed images of the respective products.