



SKINTOP® DIX-DV / SKINTOP® SD-M / SKINTOP® DV-M



SKINTOP® DIX-DV



SKINTOP® SD-M



SKINTOP® DV-M

Benefits

SKINTOP® DIX-DV

- Prevents water and dust penetrating into unused bore holes of SKINTOP® DIX-M multiple sealing inserts

SKINTOP® SD-M

- Prevents dust and dirt from getting into the housing

SKINTOP® DV-M

- Prevents humidity from seeping into the housing

Application range

SKINTOP® DIX-DV

- For inserting into unoccupied holes of the SKINTOP® DIX-M multiple sealing inserts, to ensure protection class.

SKINTOP® SD-M

- This dust protector can be placed under the cap nut of below mentioned SKINDICHT® types and specified SKINTOP® cable glands.
- Preparations
- Protection of unused connection points

SKINTOP® DV-M

- These seals are placed into the sealing ring of the SKINTOP® cable glands.
- Preparations
- Protection of unused connection points

Note

SKINTOP® DIX-DV

- When assembled professionally and properly, the protection class of IP 68 can be reached
- Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

SKINTOP® SD-M

- Easy to handle, without disassembly - push cable through
- Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

SKINTOP® DV-M

- When assembled professionally and properly, the protection class of IP 68 can be reached
- Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical data



Classification

ETIM 5.0 Class-ID: EC000032
ETIM 5.0 Class-Description:
Plug for cable screw gland



Colour delivered

SKINTOP® DIX-DV
natural
SKINTOP® SD-M
Black
SKINTOP® DV-M
Black



Material

SKINTOP® DIX-DV
Polyamide
SKINTOP® SD-M
PE foam
SKINTOP® DV-M
CR



Protection rating

SKINTOP® DIX-DV
IP 54



Temperature range

SKINTOP® DIX-DV
-40°C to +100°C
SKINTOP® SD-M
-70°C to +100°C
SKINTOP® DV-M
-30°C to +100°C

Article number	Article designation / size	Ø-F mm	Height (mm)	Pieces / PU
SKINTOP® DIX-DV				
53100003	DIX-DV 3 x 9	3.0	9	100
53100004	DIX-DV 4 x 9	4.0	9	100
53100005	DIX-DV 5 x 11	5.0	11	100
53100055	DIX-DV 5,5 x 11	5.5	11	100
53100006	DIX-DV 6 x 14	6.0	14	100
53100007	DIX-DV 7 x 14	7.0	14	100
53100008	DIX-DV 8 x 14	8.0	14	100
53100009	DIX-DV 9 x 14	9.0	14	100
SKINTOP® SD-M				
54113100	12	11.5	2	100
54113110	16	15.0	2	100
54113120	20	20.0	2	100
54113130	25	25.0	2	50
54113140	32	30.0	2	50
54113150	40	40.0	2	25
54113160	50	49.0	2	25
54113170	63	58.0	2	25
SKINTOP® DV-M				
54113000	12	7.2	7	500
54113010	16	10.0	8	500
54113020	20	13.2	8.4	250
54113030	25	17.2	9.5	250
54113040	32	21.2	12	250
54113050	40	28.2	14.5	100
54113060	50	35.8	18	100
54113070	63	45.6	20	50

Photographs are not to scale and do not represent detailed images of the respective products.

Accessories

SKINTOP® DIX-DV

- SKINTOP® CLICK refer to page 715
- SKINTOP® DIX-M refer to page 740
- SKINTOP® MS-M refer to page 724
- SKINTOP® ST-M refer to page 712
- SKINTOP® BS-M METAL / SKINTOP® BSR-M METAL refer to page 726