



SKINDICHT® STK



Benefits

- Prevents dust and dirt from getting into the housing

Application range

- This dust protector can be placed under the cap nut of below mentioned SKINDICHT® types and specified SKINTOP® cable glands.

Note

- Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical data

	Classification ETIM 5.0 Class-ID: EC000032 ETIM 5.0 Class-Description: Plug for cable screw gland
	Colour delivered White
	Material PVC
	Temperature range -20°C to +80°C

Article number	Article designation / size	Thread, male PG	Suitable for SKINDICHT® SVRN-M, SHZ-M, SKZ-M, SVR-M, SVRE-M, SHVE-M, SHV-M	Pieces / PU
SKINDICHT® STK				
52020818	STK 7	7	M 12	500
52020820	STK 9	9	M 16	500
52020830	STK 11	11	M 20 / 11	250
52020840	STK 13,5	13	M 20 / 13,5	250
52020850	STK 16	16	M 20 / 16	250
52020860	STK 21	21	M 25	250
52020870	STK 29	29	M 32	100
52020880	STK 36	36	M 40	100
52020890	STK 42	42	M 50	50
52020900	STK 48	48	M 63	50

Photographs are not to scale and do not represent detailed images of the respective products.

SKINDICHT® E



Benefits

- One seal for several clamping ranges
- Rings can be individually adapted to various cable diameters

Application range

- Incised sealing ring for SKINDICHT® cable glands

Note

- Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical data

	Classification ETIM 5.0 Class-ID: EC001181 ETIM 5.0 Class-Description: Sealing ring
	Colour delivered Black
	Material CR
	Temperature range -20°C to +80°C

Article number	Article designation / size	Outer diameter x bores (mm)	Thickness (mm)	Pieces / PU
SKINDICHT® E				
52005780	E 9	13.5 x 5/8	5.5	250
52003690	E 11	16.5 x 7 / 10 / 12.5	6.0	250
52003700	E 13,5	18.5 x 7 / 10.5 / 13 / 16	6.5	250
52003710	E 16	20.5 x 8 / 10.5 / 13.5 / 16	7.5	250
52003720	E 21	26.0 x 11 / 15 / 18 / 20	8.0	100
52003730	E 29	35.0 x 19 / 23 / 27 / 31	9.5	100
52003740	E 36	45.0 x 25 / 28 / 31 / 35	12.0	50
52005790	E 42	52.0 x 35.5 / 39 / 42.5 / 46	14.0	50
52005800	E 48	57.0 x 40.5 / 44 / 47 / 50.5	14.0	50

Photographs are not to scale and do not represent detailed images of the respective products.