



SKINDICHT® EV

Benefits

- One seal for several clamping ranges
- Rings can be individually adapted to various cable diameters
- For high temperatures
- Resistant to oils, solvents, acids and chemicals

Application range

- Incised sealing ring made of VITON® for SKINDICHT® cable glands

Note

- Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical data



Classification

ETIM 5.0 Class-ID: EC001181
ETIM 5.0 Class-Description:
Sealing ring



Colour delivered

Red brown



Material

FKM



Temperature range

-20 °C to +200 °C



Article number	Article designation / size	Outer diameter x bores (mm)	Thickness (mm)	Pieces / PU
SKINDICHT® EV				
52010340	EV 11	7 / 10 / 12.5	6.0	50
52010350	EV 13,5	7 / 10.5 / 13 / 16	6.5	50
52010360	EV 16	8 / 10.5 / 13.5 / 16	7.5	50
52010370	EV 21	11 / 15 / 18 / 20	8.0	25
52010380	EV 29	19 / 23 / 27 / 31	9.5	25
52010390	EV 36	25 / 28 / 31 / 35	12.0	25
52010410	EV 42	35.5 / 39 / 42.5 / 46	14.0	25

Viton® is a registered trademark of DuPont de Nemours

Photographs are not to scale and do not represent detailed images of the respective products.



SKINDICHT® O-Ring Perbunan® PG

Benefits

- Resistant to oil, dust and water

Application range

- For a reliable sealing against foreign objects and liquids at the connecting thread of a gland or similar components.

Note

- Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical data



Classification

ETIM 5.0 Class-ID: EC001181
ETIM 5.0 Class-Description:
Sealing ring



Colour delivered

Black



Material

NBR
Ozone and UV-resistant



Temperature range

-20 °C to +100 °C



Article number	Article designation / size	Inner Ø x thickness Ø (mm)	Pieces / PU
SKINDICHT® O-Ring Perbunan®			
53001010	O 7	10.0 x 1.5	100
53102011	O 9	13.0 x 1.5	100
53001020	O 11	16.0 x 1.5	100
52005740	O 13,5	18.0 x 1.5	100
53001030	O 16	20.0 x 1.5	100
52005750	O 21	26.0 x 2.0	100
53001040	O 29	34.0 x 2.0	50
52005760	O 36	44.0 x 2.0	50
53001050	O 42	50.0 x 2.0	50
52005770	O 48	55.0 x 2.0	50

Perbunan® is a registered trademark of BAYER AG

Photographs are not to scale and do not represent detailed images of the respective products.