

S3M寸法一覧表

〈S3M0100A〉 選択可能な材質：アルミ

歯数	寸法(mm)							適応軸穴径 (mm) ※軸穴公差H7																				定価(円/個)										
	PD	OD	LA	W	H	F	M																					A1	A4									
24	22.92	22.16	15	11	2	26	16	4	5	6	6.35	7	8	9																					3,420	3,930		
25	23.87	23.11				28	18							6	6.35	7	8	9																			3,530	4,060
26	24.83	24.07				28	18							6	6.35	7	8	9																			3,640	4,190
28	26.74	25.98				31	20							6	6.35	7	8	9	10	11																	3,690	4,240
30	28.65	27.89				33	22							6	6.35	7	8	9	10	11	12																3,730	4,290
32	30.56	29.80				35	22							6	6.35	7	8	9	10	11	12																3,770	4,340
36	34.38	33.62				40	28							6	6.35	7	8	9	10	11	12	14	15	16													3,950	4,540
40	38.20	37.44				44	32									8	9	10	11	12	14	15	16	17													4,030	4,630
44	42.02	41.25				47	34									8	9	10	11	12	14	15	16	17	18	19	20										4,130	4,750
48	45.84	45.07				48	36									8	9	10	11	12	14	15	16	17	18	19	20	22									4,230	4,860
50	47.75	46.98				51	36									8	9	10	11	12	14	15	16	17	18	19	20	22	24	25							4,270	4,910
60	57.30	56.53				61	41									8	9	10	11	12	14	15	16	17	18	19	20	22	24	25	28	30					4,530	5,210

〈S3M0100B〉 選択可能な材質：アルミ

歯数	寸法(mm)										適応軸穴径 (mm) ※軸穴公差H7																				定価(円/個)									
	PD	OD	LA	LB	W	H	K	D	F	M																					A1	A4								
24	22.92	22.16	15	23	11	2	8	14	26	16	4	5	6																						3,800	4,370				
25	23.87	23.11						16	28	18				6	6.35	7	8																						3,920	4,510
26	24.83	24.07						16	28	18				6	6.35	7	8																						4,040	4,650
28	26.74	25.98						18	31	20				6	6.35	7	8	9																					4,100	4,720
30	28.65	27.89						20	33	22				6	6.35	7	8	9																					4,140	4,760
32	30.56	29.80						20	35	22				6	6.35	7	8	9																					4,180	4,810
36	34.38	33.62						26	40	28				6	6.35	7	8	9	10	11	12																		4,380	5,040
40	38.20	37.44						30	44	32								8	9	10	11	12	14	15															4,470	5,140
44	42.02	41.25						32	47	34								8	9	10	11	12	14	15	16	17													4,580	5,270
48	45.84	45.07						34	48	36								8	9	10	11	12	14	15	16	17													4,700	5,410
50	47.75	46.98						34	51	36								8	9	10	11	12	14	15	16	17													4,740	5,450
60	57.30	56.53						39	61	41								8	9	10	11	12	14	15	16	17	18	19	20									5,030	5,780	

〈S3M0100C〉 選択可能な材質：アルミ

歯数	寸法(mm)							適応軸穴径 (mm) ※軸穴公差H7										定価(円/個)													
	PD	OD	LA	LB	W	H	K	D	F	M											A1	A4									
14	13.37	12.61	15	23	11	2	10	16	16	10	4	5	6	6.35	7	8										3,350	3,850				
15	14.32	13.56						18	18	11	4	5	6	6.35	7	8														3,400	3,910
16	15.28	14.52						20	20	12	4	5	6	6.35	7	8														3,440	3,960
18	17.19	16.43						23	23	12	4	5	6	6.35	7	8														3,620	4,160
20	19.10	18.34						23	23	13	4	5	6	6.35	7	8	9													3,660	4,210
22	21.01	20.25						25	25	14	4	5	6	6.35	7	8	9													3,730	4,290

※青塗部はタップ長さが不足する為、準標準のセットスクリーンが付属されます。(P3参照)

●製品コード例

