

Application package

Product name	Model	Description	Supported model							
			GT27	GT25	GT25 Wide	GT25 Rugged	GT25 Handy	GT23	GT21	GT21 Wide
iQ Monozukuri ANDON *1	AP30-ADN001AA-MA	1 license	●	●	●	●	●	—	—	—
	AP30-ADN001AA-MB	5 licenses	●	●	●	●	●	—	—	—
	AP30-ADN001AA-MC	10 licenses	●	●	●	●	●	—	—	—
	AP30-ADN001AA-MD	15 licenses	●	●	●	●	●	—	—	—
	AP30-ADN001AA-ME	20 licenses	●	●	●	●	●	—	—	—

*1 Contents Publisher, project file of the GOT for iQ Monozukuri ANDON (template screens), GOT Mobile function license, and the iQ Monozukuri ANDON license are included.

Options

Product name	Model	Specifications	Supported model							
			GT27	GT25	GT25 Wide	GT25 Rugged	GT23	GT21	GT21 Wide	
Protective sheet *1	GT27-15PSGC	For 15"	●	—	—	—	—	—	—	—
	GT25-12PSGC	For 12.1"	●	●	—	—	—	—	—	—
	GT25-10PSGC	For 10.4"	●	●	—	—	—	—	—	—
	GT25-08PSGC	For 8.4"	●	●	—	—	—	—	—	—
	GT25-05PSGC	For 5.7"	●	—	—	—	—	—	—	—
	GT25-05PSGC-2	NEW For 5.7"	—	●	—	—	—	—	—	—
	GT25-10WPSGC	NEW For 10.1" wide models	—	—	●	—	—	—	—	—
	GT21-07WPSGC	NEW For 7" wide models	—	—	●	—	—	—	—	●
	GT27-15PSCC	For 15"	●	—	—	—	—	—	—	—
	GT25-12PSCC	For 12.1"	●	●	—	—	—	—	—	—
	GT25-10PSCC	For 10.4"	●	●	—	—	—	—	—	—
	GT25-08PSCC	For 8.4"	●	●	—	—	—	—	—	—
	GT25-05PSCC	For 5.7"	●	—	—	—	—	—	—	—
	GT25-05PSCC-2	NEW For 5.7"	—	●	—	—	—	—	—	—
	GT25-10WPSCC	NEW For 10.1" wide models	—	—	●	—	—	—	—	—
	GT21-07WPSCC	NEW For 7" wide models	—	—	●	—	—	—	—	●
	GT25-12PSCC-UC *9	For 12.1"	● *9	●	—	—	—	—	—	—
	GT25-10PSCC-UC *9	For 10.4"	● *9	● *9	—	—	●	—	—	—
GT25-08PSCC-UC *9	For 8.4"	●	● *9	—	—	●	—	—	—	
GT21-04RPSGC-UC	For 4.3"	● Antiglare type ● Transparent ● Without a hole for the USB environmental protection cover ● A set of 5 sheets	—	—	—	—	—	—	●	—
GT21-03PSGC-UC	For 3.8"	● Antiglare type ● Transparent ● Without a hole for the USB environmental protection cover ● A set of 5 sheets	—	—	—	—	—	—	●	—
GT21-04RPSCC-UC	For 4.3"	● Clear type ● Transparent ● Without a hole for the USB environmental protection cover ● A set of 5 sheets	—	—	—	—	—	—	●	—
GT21-03PSCC-UC	For 3.8"	● Clear type ● Transparent ● Without a hole for the USB environmental protection cover ● A set of 5 sheets	—	—	—	—	—	—	●	—
UV protective sheet (for the rugged model)	GT25T-07WPSVC	NEW For 7" rugged model	—	—	—	—	●	—	—	—
Environmental protection sheet (for the open frame model)	GT25F-12ESGS	For 12.1"	—	● *7	—	—	—	—	—	—
	GT25F-10ESGS	For 10.4"	—	● *7	—	—	—	—	—	—
	GT25F-08ESGS	For 8.4"	—	● *7	—	—	—	—	—	—
USB environmental protection cover	GT25-UCOV	For 15"/12.1"/10.4"/8.4"	●	●	—	—	—	—	—	—
	GT25-05UCOV	For 5.7"	●	—	—	—	—	—	—	—
	GT21-WUCOV	NEW For 10.1" wide models/7" wide models/5.7"	—	●	●	—	—	—	—	●
Protective cover for oil *3	GT20-15PCO	For 15"	●	—	—	—	—	—	—	—
	GT20-12PCO	For 12.1"	●	●	—	—	—	—	—	—
	GT20-10PCO	For 10.4"	●	●	—	—	—	●	—	—
	GT21-10WPCO	NEW For 10.1" wide models	—	—	●	—	—	—	—	—
	GT20-08PCO	For 8.4"	●	●	—	—	—	●	—	—
	GT21-07WPCO	NEW For 7" wide models	—	—	●	—	—	—	—	●
	GT25T-07WPCO	NEW For 7" rugged model	—	—	—	●	—	—	—	—
	GT25-05PCO	For 5.7"	●	—	—	—	—	—	—	—
	GT25-05PCO-2	NEW For 5.7"	—	●	—	—	—	—	—	—
	GT21-04RPCO	For 4.3"	—	—	—	—	—	—	—	●
GT10-20PCO	For 3.8"	—	—	—	—	—	—	—	●	
Stand	GT15-90STAND	For 15"	●	—	—	—	—	—	—	—
	GT15-80STAND	For 12.1"	●	●	—	—	—	—	—	—
	GT15-70STAND	For 10.4"/8.4"	●	●	—	—	—	●	—	—
	GT25-10WSTAND	NEW For 10.1" wide models	—	—	●	—	—	—	—	—
	GT21-07WSTAND	NEW For 7" wide models	—	—	●	—	—	—	—	●
	GT25T-07WSTAND	NEW For 7" rugged model	—	—	—	●	—	—	—	—
GT05-50STAND	For 5.7"	●	●	—	—	—	—	—	—	