

替刃

刃先形状

片刃

鋼線、鉄線等軟材の切断に適します

両刃

ステンレス線、鉄線等硬材の切断に適します

薄刃


樹脂等の切断に適します

※C寸法は多少バラツキがあります

ZCR刃



CR刃の刃面超硬タイプ
(硬線切断用)




品番	各部寸法 (mm)			刃先形状
	A	B	C	
ZCR20	24.0	10.0	2.5	片刃
ZCR2	24.0	10.0	3.0	片刃
ZCR7	26.0	10.0	3.5	片刃
ZCR4	27.0	10.0	5.0	片刃
ZCR6A	35.0	16.0	7.0	両刃
ZCR6J	35.0	16.0	5.0	両刃
ZCR6	35.0	16.0	7.0	両刃
ZCR8P1	38.0	16.0	6.0	両刃
ZCR8P	38.0	16.0	7.0	両刃
ZCR120	40.0	16.0	7.0	両刃

F-S刃



刃面ストレートタイプ
(樹脂切断用)




品番	各部寸法 (mm)			刃先形状
	A	B	C	
F10S	24.0	12.0	2.5	薄刃
F1S	24.0	12.0	3.0	薄刃
FT7S	27.0	12.0	3.5	薄刃
F3S	27.0	12.0	5.0	薄刃
F3LS	50.0	30.0	8.0	薄刃
F5AS	35.0	16.0	5.5	薄刃
F5JS	35.0	17.0	5.0	薄刃
F5S	35.0	16.0	8.5	薄刃
F5LS	65.0	37.0	15.0	薄刃
F250S	43.0	23.0	13.0	薄刃
F9P1S	66.0	39.0	10.5	薄刃
F9PS	66.0	37.0	16.0	薄刃

ZEP刃



EP刃の刃面超硬タイプ
(硬線切断用)



品番	各部寸法 (mm)			刃先形状
	A	B	C	
ZEP20	20.0	7.0	2.0	両刃
ZEP2	20.0	7.0	2.5	両刃
ZEP7	26.0	9.0	3.0	両刃
ZEP4	26.0	9.0	4.5	両刃
ZEP6A	28.0	12.0	5.0	両刃
ZEP6J	28.0	12.0	4.0	両刃
ZEP6	28.0	12.0	6.0	両刃
ZEP10P1	34.0	17.0	5.5	両刃
ZEP10P	34.0	17.0	5.5	両刃
ZEP120	40.0	25.0	8.0	両刃

FD刃



刃面角度 30°~40° タイプ
(樹脂切断用)



品番	各部寸法 (mm)				刃先形状
	A	B	C	F°	
FD10	24.0	10.0	2.5	40	薄刃
FD1	24.0	10.0	3.0	40	薄刃
FD7	27.0	10.0	3.5	40	薄刃
FD3	27.0	10.0	4.5	40	薄刃
FD5A	35.0	14.0	5.5	40	薄刃
FD5J	34.0	14.0	5.0	40	薄刃
FD5	35.0	14.0	8.5	40	薄刃
FD250	43.0	15.0	13.0	40	薄刃
FD9P1	59.0	27.0	9.0	30	薄刃
FD9P	59.0	27.0	14.0	30	薄刃
FD9PF	59.0	27.0	26.0	30	薄刃

F刃



スタンダードタイプ
(樹脂切断用)




品番	各部寸法 (mm)				刃先形状
	A	B	C	F°	
F10	24.0	12.0	2.5	15	薄刃
F1	24.0	12.0	3.0	15	薄刃
FT7	27.0	12.0	3.5	25	薄刃
F3	27.0	12.0	5.0	25	薄刃
F5A	35.0	15.0	5.5	15	薄刃
F5J	34.0	15.0	5.0	15	薄刃
F5	35.0	15.0	8.5	15	薄刃
F250	43.0	22.0	13.0	15	薄刃
F9P1	66.0	38.0	10.5	15	薄刃
F9P	66.0	38.0	16.0	15	薄刃
F9PF	66.0	38.0	30.0	15	薄刃
F120	53.0	35.0	12.0	30	薄刃

FEP刃



フイキリタイプ
(樹脂切断用)



品番	各部寸法 (mm)			刃先形状
	A	B	C	
FEP20	20.0	7.0	2.0	薄刃
FEP2	20.0	7.0	2.5	薄刃
FEP7	26.0	9.0	3.0	薄刃
FEP4	26.0	9.0	4.5	薄刃
FEP6A	28.0	12.0	4.0	薄刃
FEP6	28.0	12.0	8.5	薄刃
FEP10P1	33.0	17.0	6.0	薄刃
FEP10P	34.0	17.0	8.0	薄刃