

品番	砥材	粒度	硬度	結合剤	形状	寸法(mm)		周速度 m/s	入数(枚)
						外径×厚み×穴径			
1000E30650	PA	80	I	V	1	305×38×127		33	3
1000E30660	PA	80	J	V	1	305×38×127		33	3
1000E30670	PA	46	H	V	1	305×50×76.2		33	2
1000E30680	PA	60	H	V	1	305×50×76.2		33	2
1000E30690	PA	46	H	V	1	305×50×127		33	2
1000E30700	PA	46	I	V	1	305×50×127		33	2
1000E30710	PA	46	J	V	1	305×50×127		33	2
1000E32830	PA	60	J	V	1	305×50×127		33	2
1000E30720	PA	46	J	V	1	355×25×76.2		33	2
※ 1000E30730	PA	60	I	V	1	355×25×76.2		33	2
1000E30740	PA	60	J	V	1	355×25×76.2		33	2
※ 1000E30750	PA	60	K	V	1	355×25×76.2		33	2
1000E30760	PA	60	I	V	1	355×25×127		33	2
1000E30770	PA	60	J	V	1	355×25×127		33	2
※ 1000E30780	PA	60	K	V	1	355×25×127		33	2
1000E30790	PA	80	K	V	1	355×25×127		33	2
1000E30800	PA	46	I	V	1	355×32×127		33	2
1000E30810	PA	46	J	V	1	355×32×127		33	2
1000E30820	PA	60	I	V	1	355×32×127		33	2
1000E30830	PA	60	J	V	1	355×32×127		33	2
※ 1000E30840	PA	60	K	V	1	355×32×127		33	2
1000E30850	PA	60	J	V	1	355×32×152.4		33	2
1000E30860	PA	60	K	V	1	355×32×152.4		33	2
1000E30870	PA	46	H	V	1	355×38×76.2		33	2
1000E30880	PA	46	I	V	1	355×38×76.2		33	2
1000E30890	PA	46	J	V	1	355×38×76.2		33	2
1000E30900	PA	60	J	V	1	355×38×76.2		33	2
※ 1000E30910	PA	60	K	V	1	355×38×76.2		33	2
1000E30920	PA	46	H	V	1	355×38×127		33	2
1000E30930	PA	46	I	V	1	355×38×127		33	2
1000E30940	PA	46	J	V	1	355×38×127		33	2
1000E30950	PA	46	K	V	1	355×38×127		33	2
1000E30960	PA	60	H	V	1	355×38×127		33	2
1000E30970	PA	60	I	V	1	355×38×127		33	2
1000E30980	PA	60	J	V	1	355×38×127		33	2
1000E30990	PA	60	K	V	1	355×38×127		33	2
1000E31000	PA	80	J	V	1	355×38×127		33	2
1000E31010	PA	80	K	V	1	355×38×127		33	2
1000E31020	PA	46	H	V	1	355×50×127		33	1
1000E31030	PA	46	I	V	1	355×50×127		33	1
1000E31040	PA	46	J	V	1	355×50×127		33	1
1000E31050	PA	60	H	V	1	355×50×127		33	1
1000E31060	PA	60	I	V	1	355×50×127		33	1
1000E31070	PA	60	J	V	1	355×50×127		33	1
1000E31080	PA	60	K	V	1	355×50×127		33	1

品番	砥材	粒度	硬度	結合剤	形状	寸法(mm)		周速度 m/s	入数(枚)
						外径×厚み×穴径			
1000E31090	PA	80	J	V	1	355×50×127		33	1
※ 1000E31100	PA	80	K	V	1	355×50×127		33	1
1000E31110	PA	80	K	V	1	405×25×152.4		33	1
1000E31120	PA	80	J	V	1	405×38×127		33	1
1000E31130	PA	80	K	V	1	405×38×152.4		33	1
1000E31140	PA	60	J	V	1	405×38×203.2		33	1
1000E31150	PA	60	K	V	1	405×38×203.2		33	1
1000E31160	PA	80	K	V	1	405×38×203.2		33	1
1000E31170	PA	46	H	V	1	405×50×127		33	1
1000E31180	PA	46	I	V	1	405×50×127		33	1
1000E31190	PA	46	J	V	1	405×50×127		33	1
1000E31200	PA	60	H	V	1	405×50×127		33	1
1000E31210	PA	60	J	V	1	405×50×127		33	1
※ 1000E31220	PA	60	K	V	1	405×50×127		33	1
1000E31230	PA	80	J	V	1	405×50×127		33	1
1000E31240	PA	80	K	V	1	405×50×127		33	1
1000E31250	PA	60	J	V	1	405×50×152.4		33	1
※ 1000E31260	PA	60	K	V	1	405×50×152.4		33	1
1000E31270	PA	80	J	V	1	405×50×152.4		33	1
1000E31280	PA	80	K	V	1	405×50×152.4		33	1
1000E31290	PA	60	H	V	1	405×50×203.2		33	1
1000E31300	PA	46	H	V	1	510×50×127		33	1
1000E31310	PA	46	I	V	1	510×50×127		33	1
1000E32840	PA	46	J	V	1	510×50×127		33	1
1000E32850	PA	60	J	V	1	510×50×127		33	1
1000E31590	PAA	46	I	V	1	180×6.4×31.75		40	5
1000E31600	PAA	46	J	V	1	180×6.4×31.75		40	5
1000E31610	PAA	46	K	V	1	180×6.4×31.75		40	5
1000E31620	PAA	60	H	V	1	180×6.4×31.75		40	5
1000E31630	PAA	60	J	V	1	180×6.4×31.75		40	5
1000E31640	PAA	60	K	V	1	180×6.4×31.75		40	5
1000E31650	PAA	80	H	V	1	180×6.4×31.75		40	5
1000E31660	PAA	80	J	V	1	180×6.4×31.75		40	5
1000E31670	PAA	80	K	V	1	180×6.4×31.75		40	5
※ 1000E31680	PAA	100	I	V	1	180×6.4×31.75		40	5
1000E31690	PAA	100	J	V	1	180×6.4×31.75		40	5
1000E31700	PAA	100	K	V	1	180×6.4×31.75		40	5
1000E31710	PAA	120	I	V	1	180×6.4×31.75		40	5
1000E31720	PAA	120	J	V	1	180×6.4×31.75		40	5
1000E31730	PAA	120	K	V	1	180×6.4×31.75		40	5
1000E31740	PAA	150	J	V	1	180×6.4×31.75		40	5
1000E31750	PAA	150	K	V	1	180×6.4×31.75		40	5
1000E31760	PAA	180	J	V	1	180×6.4×31.75		40	5
1000E31770	PAA	180	K	V	1	180×6.4×31.75		40	5
1000E31780	PAA	220	K	V	1	180×6.4×31.75		40	5

切断砥石

オフセット砥石

ビットフライド砥石

ビットホイール

ダイヤモンド工具

ドレッシング工具

周辺機器

研削油

フリップディスク

研磨材

選定表

技術資料