

NK-1200 Multiuse Union Type (Female Both Ends)

DN: 6mm(1/8") ~ 100mm(4")
 Length: 200mm ~ 10M
 *For any other specifications, please contact us.



① Tube	Stainless Steel
② Braid	Stainless Steel
③ Ring	Stainless Steel
④ Union	Carbon Steel, Stainless Steel
⑤ Gasket	Non Asbestos

NK-1300 Female Threaded Type

DN: 6mm(1/8") ~ 65mm(2.5")
 Length: 200mm ~ 10M
 *For any other specifications, please contact us.



① Tube	Stainless Steel
② Braid	Stainless Steel
③ Ring	Stainless Steel
④ Socket	Carbon Steel, Stainless Steel

NK-1500 Male Threaded Type

DN: 6mm(1/8") ~ 50mm(2")
 Length: 200mm ~ 10M
 *For any other specifications, please contact us.



① Tube	Stainless Steel
② Braid	Stainless Steel
③ Ring	Stainless Steel
④ Nipple	Carbon Steel, Stainless Steel

Threaded Type Flexible Hose

F1

Flange Type Flexible Hose

F2

Fire Law Flexible Hose

F3

Quick Connection Flexible Hose

F4

Flexible Hose for Vacuums

F5

Flexible Hose with Fluororesin

F6

Other Flexible Hose

F7