

4-3 Model list

- The box (●) in the model name indicates **B** (horizontal to mounting foot surface) or **F** (vertical to mounting foot surface) representing the rack moving direction.
- The box (■) in the model name indicates **A** (standard) or **M** (with electromagnetic brake) representing the motor type.

■ AC power input type

High-speed type

Rack maximum speed	Rack and pinion motor model
500 mm/s	LM2●500AZ■C-1
	LM2●500AZ■C-2
	LM2●500AZ■C-3
	LM2●500AZ■C-4
	LM2●500AZ■C-5
	LM2●500AZ■C-6
	LM2●500AZ■C-7
	LM2●500AZ■C-8
	LM4●500AZ■C-1
	LM4●500AZ■C-2
	LM4●500AZ■C-3
	LM4●500AZ■C-4
	LM4●500AZ■C-5
	LM4●500AZ■C-6
	LM4●500AZ■C-7
	LM4●500AZ■C-8
	LM4●500AZ■C-9
	LM4●500AZ■C-10

Large transportable mass type

Rack maximum speed	Rack and pinion motor model
90 mm/s	LM2●90AZ■C-1
	LM2●90AZ■C-2
	LM2●90AZ■C-3
	LM2●90AZ■C-4
	LM2●90AZ■C-5
	LM2●90AZ■C-6
	LM2●90AZ■C-7
	LM2●90AZ■C-8
40 mm/s	LM4●40AZ■C-1
	LM4●40AZ■C-2
	LM4●40AZ■C-3
	LM4●40AZ■C-4
	LM4●40AZ■C-5
	LM4●40AZ■C-6
	LM4●40AZ■C-7
	LM4●40AZ■C-8
	LM4●40AZ■C-9
	LM4●40AZ■C-10

■ DC power input type

High-speed type

Rack maximum speed	Rack and pinion motor model
200 mm/s	LM2●200AZ■K-1
	LM2●200AZ■K-2
	LM2●200AZ■K-3
	LM2●200AZ■K-4
	LM2●200AZ■K-5
150 mm/s	LM4●150AZ■K-1
	LM4●150AZ■K-2
	LM4●150AZ■K-3
	LM4●150AZ■K-4
	LM4●150AZ■K-5
	LM4●150AZ■K-6
	LM4●150AZ■K-10

Large transportable mass type

Rack maximum speed	Rack and pinion motor model
50 mm/s	LM2●50AZ■K-1
	LM2●50AZ■K-2
	LM2●50AZ■K-3
	LM2●50AZ■K-4
	LM2●50AZ■K-5
20 mm/s	LM4●20AZ■K-1
	LM4●20AZ■K-2
	LM4●20AZ■K-3
	LM4●20AZ■K-4
	LM4●20AZ■K-5
	LM4●20AZ■K-6
	LM4●20AZ■K-10