

Plate Type Rubber Casters (for light/medium load)

Stock 646Items

2-647

Prices displayed include 8% tax.

TRUSCO Stock 38,650 Items

Plate Type Caster "TYS Series" (press made rubber wheel)

Com Drawing



TYS rubber integrated wheel type



TYS steel wheel rubber tire type



TYSB rubber integrated wheel type



TYSB steel wheel rubber tire type







TYSK rubber integrated wheel type



TYSK steel wheel rubber tire type



TYSW Type



Features •A standard caster with driveability and load capacity for light/medium load. A standard dimension caster used a lot for transportation dollies, roll box pallets and other general work uses.

- Specs •Plate Type
Materials •Metal Fitting: Steel
•Metal Fitting Surface Treatment: Trivalent Unichrome Plated
•Wheel: Rubber
Origin •Japan

Bearing structure of pivot portion



Wheel diameter (mm)	Wheel Shape
50, 65, 75	Rubber-Integrated Wheel
100, 125, 150	Steel wheel rubber tire

Flexible Specs •Flexible Type

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Allowable Weight		Wheel Diameter D (mm)	Wheel Width (mm)	Mounting Height H (mm)	Mounting Plate A x B (mm)	Mounting Pitch X x Y (mm)	Mounting Hole Diameter P (mm)	SPQ (piece)	Weight (g)
				(daN)	(kgf)								
474-8166	TYS-50	¥ 417	¥ 450	50	51.0	50	28	70	70 x 58	55 x 42	8.8	20	280
474-8174	TYS-65	¥ 472	¥ 510	50	51.0	65	25	85	70 x 58	55 x 42	8.8	20	330
474-8182	TYS-75	¥ 528	¥ 570	60	61.2	75	25	93	70 x 58	55 x 42	8.8	20	365
474-8191	TYS-100	¥1,203	¥1,300	120	122.4	100	32	132	90 x 90	68 to 71 x 68 to 71	11.0	20	840
474-8204	TYS-125	¥1,713	¥1,850	150	153.0	125	38	168	102 x 102	75 to 80 x 75 to 80	11.0	10	1200
474-8212	TYS-150	¥1,898	¥2,050	160	163.2	150	40	190	102 x 102	75 to 80 x 75 to 80	11.0	10	1410

TRUSCO NAKAYAMA CORPORATION

Flexible with stopper Specs •Flexible Type (with stopper)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Allowable Weight		Wheel Diameter D (mm)	Wheel Width (mm)	Mounting Height H (mm)	Mounting Plate A x B (mm)	Mounting Pitch X x Y (mm)	Mounting Hole Diameter P (mm)	SPQ (piece)	Weight (g)
				(daN)	(kgf)								
474-8221	TYSB-50	¥ 528	¥ 570	50	51.0	50	28	70	70 x 58	55 x 42	8.8	20	310
474-8239	TYSB-65	¥ 583	¥ 630	50	51.0	65	25	85	70 x 58	55 x 42	8.8	20	380
474-8247	TYSB-75	¥ 648	¥ 700	60	61.2	75	25	93	70 x 58	55 x 42	8.8	20	420
474-8255	TYSB-100	¥1,481	¥1,600	120	122.4	100	32	132	90 x 90	68 to 71 x 68 to 71	11.0	20	935
474-8263	TYSB-125	¥2,019	¥2,180	150	153.0	125	38	168	102 x 102	75 to 80 x 75 to 80	11.0	10	1410
474-8271	TYSB-150	¥2,240	¥2,420	160	163.2	150	40	190	102 x 102	75 to 80 x 75 to 80	11.0	10	1575

Wheel diameter (mm)	Wheel Shape
50, 65, 75	Rubber-Integrated Wheel
100, 125, 150	Steel wheel rubber tire

Fixed Specs •Fixed Type

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Allowable Weight		Wheel Diameter D (mm)	Wheel Width (mm)	Mounting Height H (mm)	Mounting Plate A x B (mm)	Mounting Pitch X x Y (mm)	Mounting Hole Diameter P (mm)	SPQ (piece)	Weight (g)
				(daN)	(kgf)								
474-8280	TYSK-50	¥ 314	¥ 340	50	51.0	50	28	70	70 x 47	55 x 28	8.8	20	175
474-8298	TYSK-65	¥ 352	¥ 380	50	51.0	65	25	85	70 x 47	55 x 28	8.8	20	225
474-8301	TYSK-75	¥ 407	¥ 440	60	61.2	75	25	93	70 x 47	55 x 28	8.8	20	265
474-8310	TYSK-100	¥ 954	¥1,030	120	122.4	100	32	132	110 x 78	80 to 90 x 45 to 50	11.0	20	750
474-8328	TYSK-125	¥1,472	¥1,590	150	153.0	125	38	168	140 x 94	100 to 112 x 53 to 56	11.0	10	1075
474-8336	TYSK-150	¥1,555	¥1,680	160	163.2	150	40	190	140 x 94	100 to 112 x 53 to 56	11.0	10	1280

Wheel diameter (mm)	Wheel Shape
50, 65, 75	Rubber-Integrated Wheel
100, 125, 150	Steel wheel rubber tire

Replacement wheel Specs •With resin bush
Materials •Steel wheel, rubber

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Allowable Weight		Wheel Diameter D (mm)	Wheel Width (mm)	Hub Width B (mm)	Hole Diameter d (mm)	SPQ (piece)	Weight (g)
				(daN)	(kgf)						
484-7580	TYSW-100	¥ 778	¥ 840	120	122.4	100	32	42	12	32	450
484-7598	TYSW-125	¥1,111	¥1,200	150	153.0	125	38	55	12	16	830
484-7601	TYSW-150	¥1,231	¥1,330	160	163.2	150	40	55	12	16	1210

Contact us:0120-509-849 <http://www.orange-book.com/>