

Prices displayed include 8% tax.

TRUSCO

 Stock 38,650 Items

Round Ring Nail





 Chemical Content Inspection




TUM-3

- Features** •By hammering and fixing to a wooden wall or a strut, it can hang an item putting through a round ring.
Use •For treatment of edges of a wire, a rope, a chain, etc.
Specs •Driving Type
Materials •Stainless Steel (SUS304) **Origin** •China



Order Unit: 1 Piece

(Price revision date: Jan, 2017) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	L (mm)	H (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
300-9220	TUM-3	¥379	¥410	3	25	30	0.15	20	8
300-9238	TUM-4	¥444	¥480	4	30	35	0.20	20	15
300-9246	TUM-5	¥546	¥590	5	35	41	0.29	20	28
300-9254	TUM-6	¥658	¥710	6	40	43	0.49	20	50
300-9262	TUM-8	¥861	¥930	8	45	47	0.78	20	94

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO

 Stock 38,650 Items

Round Ring Screw





 Chemical Content Inspection




TMS-5M

- Features** •With screw processing, screwing directly into wood is possible.
Use •Install on wooden walls, floor surfaces, and pillars, etc. as a terminal metal fitting for a chain, wire, and rope.
Specs •Threaded type
Materials •Stainless Steel (SUS304)
Origin •China



Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	L (mm)	H (mm)	d (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
328-5901	TMS-3M	¥ 518	¥ 560	3	25	45	4	0.15	20	9
328-5910	TMS-5M	¥ 741	¥ 800	5	30	55	6	0.29	20	28
328-5928	TMS-7M	¥1,074	¥1,160	7	50	56	8	0.69	20	79

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO

 Stock 38,650 Items

Long Eye Screw





 Chemical Content Inspection




TIS-L3

- Features** •Screw directly into the wall of a wooden frame.
Use •Wooden walls, floors, and pillars, etc.
Specs •Threaded type
Materials •Stainless Steel (SUS304)
Origin •China



Order Unit: 1 Piece

(Price revision date: Jan, 2017) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	L (mm)	H (mm)	B (mm)	E (mm)	A (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
300-9149	TIS-L3	¥ 648	¥ 700	3.5	8.5	16	35	2.8	9	0.15	20	5
300-9157	TIS-L4	¥ 676	¥ 730	4.0	10.0	20	41	4.0	10	0.20	20	8
300-9165	TIS-L5	¥ 787	¥ 850	5.0	13.0	26	50	5.0	11	0.29	20	16
300-9173	TIS-L6	¥ 944	¥1,020	5.0	16.0	28	50	6.0	12	0.59	20	21
300-9181	TIS-L8	¥1,268	¥1,370	7.0	19.5	34	55	8.0	15	0.78	20	40

Contact us:0120-509-849 <http://www.orange-book.com/>

MIZUMOTO MACHINE

 Stock 529 Items

Eye Screw





 Chemical Content Inspection



B-1141

- Features** •Screw directly into the wall of a wooden frame.
Use •Install on wooden walls, floor surfaces, and pillars, etc. as a terminal metal fitting for a chain, wire, and rope.
Specs •Threaded type
Materials •Stainless Steel (SUS304) **Origin** •China



Order Unit: 1 Piece

(Price revision date: Jan, 2016) MIZUMOTO MACHINE MFG.Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	L (mm)	H (mm)	B (mm)	E (mm)	A (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
378-8156	B-1139	¥671	¥790	3.5	8.5	16	20	2.8	9	0.15	20	5
378-8164	B-1140	¥713	¥840	4.0	10.0	20	25	4.0	10	0.20	20	7
378-8172	B-1141	¥832	¥980	5.0	13.0	26	30	5.0	11	0.29	20	14

Contact us:079-246-2501 <http://www.mizumoto-mm.co.jp/>

MIZUMOTO MACHINE

 Stock 529 Items

Long Eye Screw





 Chemical Content Inspection



B-2159

- Features** •Screw directly into the wall of a wooden frame.
Use •Wooden walls, floors, and pillars, etc.
Specs •Threaded type
Materials •Stainless Steel (SUS304) **Origin** •China



Order Unit: 1 Piece

(Price revision date: Jan, 2016) MIZUMOTO MACHINE MFG.Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	L (mm)	H (mm)	B (mm)	E (mm)	A (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
378-9543	B-2159	¥1,850	¥2,180	8	24	41	75	10	19	1.47	10	85

Contact us:079-246-2501 <http://www.mizumoto-mm.co.jp/>