

TRUSCO



Stock 38,650 Items

Ring Catch



TRK-08 (with ring)

- Features • You can easily open and close by turning the nut.
 Use • As joint metal fittings, for attaching chains and the like.
 Materials • **Steel**
 • **Surface Treatment: Unichrome**
 Origin • **China**

Order Unit: 1 Piece

(Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	L1 (mm)	B1 (mm)	S (mm)	E (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
275-7915	TRK-035	¥231	¥250	3.5	29	9.5	5.0	5.0	0.40	30	8.3
275-7923	TRK-04	¥259	¥280	4.0	33	10.5	5.0	5.5	0.50	30	12.3
275-7931	TRK-05	¥269	¥290	5.0	38	12.0	6.5	6.5	0.70	30	20.5
275-7940	TRK-06	¥278	¥300	6.0	46	13.5	7.5	8.0	0.90	30	33.0
275-7958	TRK-08	¥417	¥450	8.0	58	16.0	9.5	10.5	1.50	30	77.0
275-7966	TRK-09	¥472	¥510	9.0	63	18.0	10.5	12.0	2.00	30	103.2
275-7974	TRK-010	¥694	¥750	10.0	70	18.0	11.5	13.5	2.50	30	137.4
275-7982	TRK-012	¥713	¥770	12.0	83	22.0	13.5	15.5	3.50	30	232.8

Door Closers

Door Stoppers

Hinges

Slide Bolt Latches

Catches

Handles

Keys

Chains

Wire Ropes

Metal Fittings for Handling

Suspension Metal Fittings

Shelf Peg Metal Fittings

Joint Fittings

Steel Wires

Wire Nets

Inspection Doors, Air Inlet/Outlets

Handrails, Slopes

Corrugated Plates

Plastic Materials

Metal Materials

Construction Materials

Sash Rollers

Door Hangers

Estimated Unit Price per Piece
¥173 to ¥339



Packaged in a Box

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	D (mm)	L1 (mm)	B1 (mm)	S (mm)	E (mm)	Working Load (kN)	Q'ty Per Box (piece)	SPQ (box)	Weight (kg/box)
470-3081	TRK-035-30P	¥ 5,184	¥ 5,600	3.5	29	9.5	5.0	5.0	0.40	30	1	0.25
470-3090	TRK-04-30P	¥ 5,832	¥ 6,300	4.0	33	10.5	5.0	5.5	0.50	30	1	0.37
470-3103	TRK-05-30P	¥ 6,295	¥ 6,800	5.0	38	12.0	6.5	6.5	0.70	30	1	0.62
470-3111	TRK-06-30P	¥ 6,943	¥ 7,500	6.0	46	13.5	7.5	8.0	0.90	30	1	0.99
470-3120	TRK-08-30P	¥10,183	¥11,000	8.0	58	16.0	9.5	10.5	1.50	30	1	2.31

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO



Stock 38,650 Items

Ring Catch



TRC-6 (with ring)

- Features • You can easily open and close by turning the nut.
 Use • As joint brackets, for attaching to edges such as chains, etc.
 Specs • Both screw type
 Materials • **Stainless Steel (SUS304)**

Item No.	Origin
TRC-2.5 to TRC-13	China
TRC-16 TRC-19	Japan

Order Unit: 1 Bag

(Price revision date: Jan, 2017) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	D (mm)	L (mm)	B1 (mm)	B2 (mm)	S (mm)	E (mm)	Working Load (kN)	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
274-9718	TRC-2.5	¥ 1,065	¥ 1,150	2.5	25.5	9	8.0	4.5	2.7	0.15	2	20	8
274-9726	TRC-3	¥ 1,361	¥ 1,470	3.0	29.0	10	8.5	5.5	3.3	0.29	2	20	12
274-9734	TRC-4	¥ 1,435	¥ 1,550	4.0	34.0	11	9.5	6.5	4.4	0.49	2	20	22
274-9742	TRC-5	¥ 1,630	¥ 1,760	5.0	42.0	13	11.5	8.5	5.4	0.78	2	20	40
274-9751	TRC-6	¥ 1,796	¥ 1,940	6.0	49.0	15	13.5	9.5	6.5	1.47	2	20	64
274-9769	TRC-8	¥ 1,371	¥ 1,480	8.0	62.0	17	15.0	10.5	8.5	3.43	1	20	72
274-9777	TRC-9	¥ 1,879	¥ 2,030	9.0	67.0	20	18.0	11.5	9.5	4.90	1	20	101
274-9785	TRC-10	¥ 2,462	¥ 2,660	10.0	76.0	22	20.0	13.0	10.5	6.86	1	10	139
274-9793	TRC-11	¥ 3,203	¥ 3,460	11.0	85.0	24	22.0	14.0	11.6	7.84	1	10	179
274-9807	TRC-13	¥ 3,639	¥ 3,930	13.0	96.0	27	25.0	16.0	14.0	9.80	1	10	283
856-4067	TRC-16	¥ 9,257	¥10,000	16.0	118.0	34	30.5	18.0	19.4	14.70	1	5	572
856-4068	TRC-19	¥20,181	¥21,800	19.0	142.0	41	38.0	23.5	21.5	19.60	1	5	880

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO



Stock 38,650 Items

Ring Catch "Wide Speed Catch"



TSC-6W (with ring)

- Features • You can easily open and close by turning the nut.
 • The opening of the opening is wider than the common ring catch, and easy-to-do the connection work type.
 Use • Suitable for connection of chain/wire/rope, etc., and joint of terminal metal fittings.
 Specs • One-side screw type
 Materials • **Stainless Steel (SUS304)**
 Origin • **China**

Order Unit: 1 Piece

(Price revision date: Jan, 2017) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	L (mm)	B1 (mm)	B2 (mm)	S (mm)	E (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
328-6002	TSC-3W	¥ 768	¥ 830	3	42	10.5	9.0	9	4.4	0.29	20	8
328-6011	TSC-4W	¥ 870	¥ 940	4	52	14.5	12.5	12	5.9	0.49	20	18
328-6029	TSC-5W	¥ 962	¥1,040	5	65	21.0	18.0	15	6.8	0.78	20	31
328-6037	TSC-6W	¥1,166	¥1,260	6	79	21.5	19.5	18	7.5	1.47	20	51
328-6045	TSC-8W	¥1,685	¥1,820	8	101	28.5	26.0	24	9.8	3.43	10	115

Contact us:0120-509-849 <http://www.orange-book.com/>

Dimensions

