

Polyurethane Tubes

The number next to the logo mark indicates items in stock for each brand.



Description of the coupling in the pressurized state leads to serious accident.



Stock 38,650 Items

Polyurethane Tube



- Features**
- Excellent in water resistance and oil resistance.
 - Excellent in flexibility, very small bending radius, and easy to handle.
- Specs**
- Because cut marks are displayed at 1m intervals, useful for cutting work.
 - Working Fluid: Water, Air
 - Working Temperature Range: -5 to 60°C (air), 5 to 40°C (water)
 - Maximum Working Pressure: 0.8MPa (air), 0.3MPa (water)
- Materials**
- Main Body: Polyurethane
- Origin**
- Japan



TEN-4X2.5-10: B (blue)



TEN-4X2.5-10: BK (black)



TEN-4X2.5-10: CBL (clear blue)



TEN-4X2.5-10: GN (green)



TEN-4X2.5-10: LG (light green)



TEN-4X2.5-10: O (orange)



TEN-4X2.5-10: R (red)



TEN-4X2.5-10: TM (transparent)



TEN-4X2.5-10: W (white)



TEN-4X2.5-10: Y (yellow)

Order Unit: 1 Roll

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Options (Color)	Price (per roll)	MSRP (per roll)	Color	Outer Diameter x Inner Diameter (mm)	Total Length (m)	Min Bend Radius (mm)	SPQ (roll)	Weight (g)
231-7389	TEN-4X2.5-10	B	¥ 750	¥ 810	Blue	4 x 2.5	10	5	10	90
231-7397	TEN-4X2.5-10	BK	¥ 750	¥ 810	Black	4 x 2.5	10	5	10	90
231-7401	TEN-4X2.5-10	CBL	¥ 750	¥ 810	Clear Blue	4 x 2.5	10	5	10	90
231-7419	TEN-4X2.5-10	GN	¥ 750	¥ 810	Green	4 x 2.5	10	5	10	90
231-7427	TEN-4X2.5-10	LG	¥ 750	¥ 810	Light Green	4 x 2.5	10	5	10	90
231-7435	TEN-4X2.5-10	O	¥ 750	¥ 810	Orange	4 x 2.5	10	5	10	90
231-7443	TEN-4X2.5-10	R	¥ 750	¥ 810	Red	4 x 2.5	10	5	10	90
231-7451	TEN-4X2.5-10	TM	¥ 750	¥ 810	Transparent	4 x 2.5	10	5	10	90
231-7460	TEN-4X2.5-10	W	¥ 750	¥ 810	White	4 x 2.5	10	5	10	90
231-7478	TEN-4X2.5-10	Y	¥ 750	¥ 810	Yellow	4 x 2.5	10	5	10	90
231-6561	TEN-6-10	B	¥ 1,250	¥ 1,350	Blue	6 x 4.0	10	12	10	190
231-6587	TEN-6-10	BK	¥ 1,250	¥ 1,350	Black	6 x 4.0	10	12	10	190
231-6609	TEN-6-10	CBL	¥ 1,250	¥ 1,350	Clear Blue	6 x 4.0	10	12	10	190
231-6625	TEN-6-10	GN	¥ 1,250	¥ 1,350	Green	6 x 4.0	10	12	10	190
231-6641	TEN-6-10	LG	¥ 1,250	¥ 1,350	Light Green	6 x 4.0	10	12	10	190
231-6668	TEN-6-10	O	¥ 1,250	¥ 1,350	Orange	6 x 4.0	10	12	10	190
231-6684	TEN-6-10	R	¥ 1,250	¥ 1,350	Red	6 x 4.0	10	12	10	190
231-6706	TEN-6-10	TM	¥ 1,250	¥ 1,350	Transparent	6 x 4.0	10	12	10	190
231-6722	TEN-6-10	W	¥ 1,250	¥ 1,350	White	6 x 4.0	10	12	10	190
231-6749	TEN-6-10	Y	¥ 1,250	¥ 1,350	Yellow	6 x 4.0	10	12	10	190
231-6765	TEN-8-10	B	¥ 1,907	¥ 2,060	Blue	8 x 5.0	10	15	10	370
231-6781	TEN-8-10	BK	¥ 1,907	¥ 2,060	Black	8 x 5.0	10	15	10	370
231-6803	TEN-8-10	CBL	¥ 1,907	¥ 2,060	Clear Blue	8 x 5.0	10	15	10	370
231-6820	TEN-8-10	GN	¥ 1,907	¥ 2,060	Green	8 x 5.0	10	15	10	370
231-6846	TEN-8-10	LG	¥ 1,907	¥ 2,060	Light Green	8 x 5.0	10	15	10	370
231-6862	TEN-8-10	O	¥ 1,907	¥ 2,060	Orange	8 x 5.0	10	15	10	370
231-6889	TEN-8-10	R	¥ 1,907	¥ 2,060	Red	8 x 5.0	10	15	10	370
231-6901	TEN-8-10	TM	¥ 1,907	¥ 2,060	Transparent	8 x 5.0	10	15	10	370
231-6927	TEN-8-10	W	¥ 1,907	¥ 2,060	White	8 x 5.0	10	15	10	370
231-6943	TEN-8-10	Y	¥ 1,907	¥ 2,060	Yellow	8 x 5.0	10	15	10	370
231-6960	TEN-10-10	B	¥ 2,731	¥ 2,950	Blue	10 x 6.5	10	25	5	550
231-6986	TEN-10-10	BK	¥ 2,731	¥ 2,950	Black	10 x 6.5	10	25	5	550
231-7001	TEN-10-10	CBL	¥ 2,731	¥ 2,950	Clear Blue	10 x 6.5	10	25	5	550
231-7028	TEN-10-10	GN	¥ 2,731	¥ 2,950	Green	10 x 6.5	10	25	5	550
231-7044	TEN-10-10	LG	¥ 2,731	¥ 2,950	Light Green	10 x 6.5	10	25	5	550
231-7061	TEN-10-10	O	¥ 2,731	¥ 2,950	Orange	10 x 6.5	10	25	5	550
231-7087	TEN-10-10	R	¥ 2,731	¥ 2,950	Red	10 x 6.5	10	25	5	550
231-7109	TEN-10-10	TM	¥ 2,731	¥ 2,950	Transparent	10 x 6.5	10	25	5	550
231-7125	TEN-10-10	W	¥ 2,731	¥ 2,950	White	10 x 6.5	10	25	5	550
231-7141	TEN-10-10	Y	¥ 2,731	¥ 2,950	Yellow	10 x 6.5	10	25	5	550
231-7168	TEN-12-10	B	¥ 4,008	¥ 4,330	Blue	12 x 8.0	10	28	5	760
231-7184	TEN-12-10	BK	¥ 4,008	¥ 4,330	Black	12 x 8.0	10	28	5	760
231-7206	TEN-12-10	CBL	¥ 4,008	¥ 4,330	Clear Blue	12 x 8.0	10	28	5	760
231-7222	TEN-12-10	GN	¥ 4,008	¥ 4,330	Green	12 x 8.0	10	28	5	760
231-7249	TEN-12-10	LG	¥ 4,008	¥ 4,330	Light Green	12 x 8.0	10	28	5	760
231-7265	TEN-12-10	O	¥ 4,008	¥ 4,330	Orange	12 x 8.0	10	28	5	760
231-7281	TEN-12-10	R	¥ 4,008	¥ 4,330	Red	12 x 8.0	10	28	5	760
231-7303	TEN-12-10	TM	¥ 4,008	¥ 4,330	Transparent	12 x 8.0	10	28	5	760
231-7320	TEN-12-10	W	¥ 4,008	¥ 4,330	White	12 x 8.0	10	28	5	760
231-7346	TEN-12-10	Y	¥ 4,008	¥ 4,330	Yellow	12 x 8.0	10	28	5	760

Contact us: 0120-509-849 <http://www.orange-book.com/>