

TRUSCO



Stock 38,650 Items

## Sheet Paper



Com Drawing SDS



GBS-40



- Features**
- Hard to tear because it uses a strong cotton as a base material and optimum for rust proof ruggedness, old paint peeling, especially by hand sharpening of metal base and finish polishing.
  - Grain size P1000/P1200 is the finest grain size of the glue cloth sheet in the manual field.
  - If you cut it you can also install it on sander.
  - Can not use with water on.

- Use**
- Vehicles, ships, structural steel, metal furniture, steel furniture and equipment etc.
  - Rust removal, dirt removal, burr removal.
  - Break-in polishing of base.
  - Polishing before painting, finish polishing.

- Materials**
- Abrasive Grain: Alumina Abrasive
- Origin**
- Japan

### Including 50 pieces

Order Unit: 50 Sheets

(Price revision date: Jan, 2016) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Q'ty Per Pack (sheet)	Grain Size (P)	W x L (mm)	SPQ (sheet)	Weight (g)
132-1102	GBS-30	¥129*	¥138*	50	30	230 x 280	250	83
132-1129	GBS-40	¥107*	¥115*	50	40	230 x 280	250	63
132-1145	GBS-50	¥108*	¥116*	50	50	230 x 280	250	58
132-1161	GBS-60	¥97*	¥105*	50	60	230 x 280	250	52
132-1188	GBS-80	¥97*	¥105*	50	80	230 x 280	250	43
132-1200	GBS-100	¥87*	¥95*	50	100	230 x 280	250	38
132-1226	GBS-120	¥87*	¥95*	50	120	230 x 280	250	36
132-1242	GBS-150	¥87*	¥95*	50	150	230 x 280	250	35
132-1111	GBS-180	¥87*	¥95*	50	180	230 x 280	250	35
132-1137	GBS-220	¥87*	¥95*	50	220	230 x 280	250	31
132-1153	GBS-240	¥87*	¥95*	50	240	230 x 280	250	31
132-1170	GBS-280	¥87*	¥95*	50	280	230 x 280	250	30
132-1196	GBS-320	¥87*	¥95*	50	320	230 x 280	250	30
132-1218	GBS-400	¥87*	¥95*	50	400	230 x 280	250	28
132-1234	GBS-600	¥97*	¥105*	50	600	230 x 280	250	28
132-1251	GBS-800	¥102*	¥110*	50	800	230 x 280	250	28
157-6496	GBS-1000	¥191*	¥207*	50	1000	230 x 280	250	28
157-6500	GBS-1200	¥191*	¥207*	50	1200	230 x 280	250	28

### Including 5 pieces

Estimated Unit Price per Sheet  
¥102 to ¥212

Order Unit: 1 Bag

(Price revision date: Jan, 2016)

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Grain Size (P)	W x L (mm)	Q'ty Per Bag (sheet)	SPQ (bag)	Weight (g/bag)
352-0030	GBS-30-5P	¥717	¥775	30	230 x 280	5	1	415
352-0137	GBS-40-5P	¥606	¥655	40	230 x 280	5	1	315
352-0188	GBS-50-5P	¥611	¥660	50	230 x 280	5	1	290
352-0153	GBS-60-5P	¥561	¥605	60	230 x 280	5	1	260
352-0170	GBS-80-5P	¥561	¥605	80	230 x 280	5	1	215
352-0111	GBS-100-5P	¥509	¥550	100	230 x 280	5	1	190
352-0099	GBS-120-5P	¥509	¥550	120	230 x 280	5	1	180
352-0081	GBS-150-5P	¥509	¥550	150	230 x 280	5	1	175
352-0072	GBS-180-5P	¥509	¥550	180	230 x 280	5	1	175
352-0064	GBS-220-5P	¥509	¥550	220	230 x 280	5	1	155
352-0056	GBS-240-5P	¥509	¥550	240	230 x 280	5	1	155
352-0048	GBS-280-5P	¥509	¥550	280	230 x 280	5	1	150
352-0021	GBS-320-5P	¥509	¥550	320	230 x 280	5	1	150
352-0013	GBS-400-5P	¥509	¥550	400	230 x 280	5	1	140
352-0145	GBS-600-5P	¥561	¥605	600	230 x 280	5	1	140
352-0161	GBS-800-5P	¥611	¥660	800	230 x 280	5	1	140
352-0129	GBS-1000-5P	¥1,059	¥1,145	1000	230 x 280	5	1	140
352-0102	GBS-1200-5P	¥1,059	¥1,145	1200	230 x 280	5	1	140

### 1 Sheet

Order Unit: 1 Sheet

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Grain Size (P)	W x L (mm)	SPQ (sheet)	Weight (g)
754-8451	GBS-30-1P	¥222	¥240	30	230 x 280	1	83
754-8486	GBS-40-1P	¥190	¥205	40	230 x 280	1	63
754-8494	GBS-50-1P	¥190	¥205	50	230 x 280	1	58
754-8516	GBS-60-1P	¥176	¥190	60	230 x 280	1	52
754-8532	GBS-80-1P	¥176	¥190	80	230 x 280	1	43
754-8371	GBS-100-1P	¥166	¥180	100	230 x 280	1	38
754-8397	GBS-120-1P	¥166	¥180	120	230 x 280	1	36
754-8401	GBS-150-1P	¥166	¥180	150	230 x 280	1	35
754-8419	GBS-180-1P	¥166	¥180	180	230 x 280	1	35
754-8427	GBS-220-1P	¥166	¥180	220	230 x 280	1	31
754-8435	GBS-240-1P	¥166	¥180	240	230 x 280	1	31
754-8443	GBS-280-1P	¥166	¥180	280	230 x 280	1	30
754-8460	GBS-320-1P	¥166	¥180	320	230 x 280	1	30
754-8478	GBS-400-1P	¥166	¥180	400	230 x 280	1	28
754-8508	GBS-600-1P	¥176	¥190	600	230 x 280	1	28
754-8524	GBS-800-1P	¥194	¥210	800	230 x 280	1	28
754-8362	GBS-1000-1P	¥278	¥300	1000	230 x 280	1	28
754-8389	GBS-1200-1P	¥278	¥300	1200	230 x 280	1	28

Contact us:0120-509-849 <http://www.orange-book.com/>

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes

