


Prices displayed include 8% tax.



Stock
38,650
Items

Wheel Brush



- Features**
- The shape of the brush is a disc type, and hair is planted radially toward the outside.
 - Possible to install as long as a hole is open in the center of a disc-shaped brush and a shaft of the same diameter is attached to a tool, a machine, or the like.
- Use**
- Burring of metal surfaces, polishing, cleaning, etc.
- Specs**
- Compatible with straight grinders
- Origin** • Korea

Brass Wire

Order Unit: 1 Piece

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter (mm)	Wire Diameter (mm)	Thickness (mm)	Hole Diameter (mm)	Bristle Length (mm)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
329-1243	TB-6304	¥1,296	¥1,400	32	0.15	12	10	6.0	3000	1	19
329-1251	TB-6314	¥1,296	¥1,400	38	0.15	12	10	9.0	3000	1	24
329-1260	TB-6324	¥1,342	¥1,450	50	0.15	12	10	12.0	3000	1	39
329-1278	TB-6334	¥1,342	¥1,450	65	0.15	12	10	16.5	3000	1	59
329-1286	TB-6344	¥1,435	¥1,550	75	0.15	12	10	19.0	3000	1	79
329-1294	TB-6354	¥1,620	¥1,750	100	0.15	12	10	31.0	3000	1	99

Steel Wire

Order Unit: 1 Piece

(Price revision date: Jan, 2018)

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter (mm)	Wire Diameter (mm)	Thickness (mm)	Hole Diameter (mm)	Bristle Length (mm)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
329-1308	TB-6302	¥787	¥850	32	0.3	12	10	6.0	3000	1	19
329-1316	TB-6312	¥787	¥850	38	0.3	12	10	9.0	3000	1	27
329-1324	TB-6322	¥833	¥900	50	0.3	12	10	12.0	3000	1	44
329-1332	TB-6332	¥833	¥900	65	0.3	12	10	16.5	3000	1	69
329-1341	TB-6342	¥879	¥950	75	0.3	12	10	19.0	3000	1	94
329-1359	TB-6352	¥926	¥1,000	100	0.3	12	10	31.0	3000	1	114

Stainless Steel Wire

Order Unit: 1 Piece

(Price revision date: Jan, 2018)

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter (mm)	Wire Diameter (mm)	Thickness (mm)	Hole Diameter (mm)	Bristle Length (mm)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
329-1367	TB-6303	¥1,203	¥1,300	32	0.3	12	10	6.0	3000	1	19
329-1375	TB-6313	¥1,203	¥1,300	38	0.3	12	10	9.0	3000	1	27
329-1383	TB-6323	¥1,296	¥1,400	50	0.3	12	10	12.0	3000	1	44
329-1391	TB-6333	¥1,296	¥1,400	65	0.3	12	10	16.5	3000	1	69
329-1405	TB-6343	¥1,389	¥1,500	75	0.3	12	10	19.0	3000	1	94
329-1413	TB-6353	¥1,574	¥1,700	100	0.3	12	10	31.0	3000	1	114

Contact us: 0120-509-849 <http://www.orange-book.com/>



Stock
38,650
Items

Wheel Brush



- Features**
- The shape of the brush is a disc type, and hair is planted radially toward the outside.
 - Possible to install as long as a hole is open in the center of a disc-shaped brush and a shaft of the same diameter is attached to a tool, a machine, or the like.
- Specs**
- Compatible with double-ended, bench, and desktop electric grinders
- Origin** • Korea

Brass Plating Wire

Use • Metal surface polishing, rust remover, burring, paint removal.

Order Unit: 1 Piece

(Price revision date: Jan, 2018) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter (mm)	Wire Diameter (mm)	Thickness (mm)	Hole Diameter (mm)	Bristle Length (mm)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
856-7572	TB-6361	¥3,981	¥4,300	150	0.25	16	12.70	30.0	3800	1	540
856-7573	TB-6371	¥4,629	¥5,000	200	0.35	19	15.88	49.5	3600	1	740
856-7574	TB-6381	¥6,758	¥7,300	250	0.35	25	19.05	62.0	3600	1	1350
856-7575	TB-6391	¥10,646	¥11,500	300	0.35	32	25.40	74.5	2500	1	2100

Steel Wire

Use • Burring of metal surfaces, polishing, cleaning, etc.

Order Unit: 1 Piece

(Price revision date: Jan, 2018)

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter (mm)	Wire Diameter (mm)	Thickness (mm)	Hole Diameter (mm)	Bristle Length (mm)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
855-4898	TB-6362	¥3,055	¥3,300	150	0.3	16	12.70	30.0	3800	1	520
855-4899	TB-6372	¥3,425	¥3,700	200	0.3	19	15.88	49.5	3600	1	720
855-4900	TB-6382	¥6,758	¥7,300	250	0.3	25	19.05	62.0	3600	1	1300
855-4901	TB-6392	¥10,646	¥11,500	300	0.3	32	25.40	74.5	1800	1	1750

Stainless Steel Wire

Use • Burring of metal surfaces, polishing, cleaning, etc.

Order Unit: 1 Piece

(Price revision date: Jan, 2018)

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Outer Diameter (mm)	Wire Diameter (mm)	Thickness (mm)	Hole Diameter (mm)	Bristle Length (mm)	Max Working Rotation Speed (rpm)	SPQ (piece)	Weight (g)
855-4894	TB-6363	¥4,166	¥4,500	150	0.3	16	12.70	30.0	3800	1	520
855-4895	TB-6373	¥6,110	¥6,600	200	0.3	19	15.88	49.5	3600	1	720
855-4896	TB-6383	¥7,961	¥8,600	250	0.3	25	19.05	62.0	3600	1	1300
855-4897	TB-6393	¥11,571	¥12,500	300	0.3	32	25.40	74.5	1800	1	1750

Contact us: 0120-509-849 <http://www.orange-book.com/>