

For Fall Prevention Metal Fittings, see p. 10-165

The number next to the logo mark indicates items in stock for each brand.

TRUSCO **Stock 38,650 Items**

Com.eco Green Purchasing Chemical Content Inspection

.Com Drawing

Catalogue Case (A4 type)

FR40-G326AP FR40-G313AP

Specs

- Color: Neo Gray
- Compatible Type Fall Prevention Metal Fittings: TK/NTK Type

Materials

- Main Body: Steel
- Drawer: Resin

Origin

- Japan

Order Unit: 1 Piece | Factory direct | Freight: ¥2,000 | Excluding remote islands

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Max Load Capacity (kg/piece)	Equal Load Capacity (kg/stage)	W x D x H (mm)	Drawer	Drawers Effective Internal Dimension (mm) W x D x H	Weight (kg)
★520-6766	FR40-G326AP	¥144,967	¥156,600	180	3	880 x 400 x 1110	A4 Shallow Type 3 Rows 26 Stages	239 x 328 x 31	66.5
★520-6758	FR40-G313AP	¥122,657	¥132,500	180	3	880 x 400 x 1110	A4 Deep 3 Rows 13 Stages	239 x 327 x 70	54.0

TRUSCO NAKAYAMA CORPORATION

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

Com.eco Green Purchasing Chemical Content Inspection

.Com Drawing

Bookshelf Base

FB40-G06 FB40-G06W

Specs

- Color: Neo Gray
- Compatible Type Fall Prevention Metal Fittings: TK/NTK Type

Origin

- Japan

Order Unit: 1 Piece | Factory direct | Freight: ¥1,500 | Excluding remote islands

Order Code	Item No.	Price (per piece)	MSRP (per piece)	W x D x H (mm)	Applicable Bookshelf Dimension (mm) W x D	Weight (kg)
★520-6774	FB40-G06	¥6,110	¥6,600	880 x 380 x 60	880 x 400	3
★520-6782	FB40-G06W	¥9,072	¥9,800	1760 x 380 x 60	1760 x 400	5

TRUSCO NAKAYAMA CORPORATION

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

Partition Panel for Catalogue Case

Specs

- Up to 12 partitions (vertically 2 sheets and horizontally 3 sheets) are possible.

Materials

- PS resin

Origin

- Japan

Order Unit: 1 Sheet | Factory direct | Freight: ¥1,000 | Excluding remote islands

Partition panel for A4

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Type	Compatible Body	Weight (g)
★510-6419	A4-15L	¥472	¥510	Longitudinal	Common to shallow type A4-20 and medium-deep type A4-15H	25
★510-6427	A4-15S	¥472	¥510	Short Hand	Common to shallow type A4-20 and medium-deep type A4-15H	18
★510-6435	A4-10L	¥537	¥580	Longitudinal	Deep type A4-10	48
★510-6443	A4-10S	¥500	¥540	Short Hand	Deep type A4-10	33

TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Sheet | Factory direct | Freight: ¥1,000 | Excluding remote islands

Partition panel for B4

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Type	Compatible Body	Weight (g)
★510-6451	B4-15L	¥500	¥540	Longitudinal	Common to shallow type B4-20 and medium-deep type B4-15	28
★510-6460	B4-15S	¥500	¥540	Short Hand	Common to shallow type B4-20 and medium-deep type B4-15	19
★510-6478	B4-10L	¥565	¥610	Longitudinal	Deep type B4-10	54
★510-6486	B4-10SS	¥537	¥580	Short Hand	Deep type B4-10	36

TRUSCO NAKAYAMA CORPORATION