



Designation		轴径 Shaft Diameter	额定负荷 Basic load rating		重量 Weight (gf)		Dimensions (mm)			
Rail Units	箱式单元** Slide Units		动负荷 Dynamic C N	Static Co N	Slide Units (kgf)	导轨 Rails (kgf/m)	D	h	H	E
TBR16S	TBR16UU	16	392	490	0.18	2.45	31	22	40	25
TBR20S	TBR20UU	20	784	1176	0.30	3.60	34	29	50	27.5
TBR25S	TBR25UU	25	1568	2352	0.60	5.60	41	32	60	32.5
TBR30S	TBR30UU	30	1764	2940	0.90	8.00	45.5	36.5	70	37.5

Designation	尺寸 Dimensions (mm)												
	W	G	A	B	T	M	S <sub>1</sub>	J	K	S <sub>2</sub>	C	N	P
TBR16S	62	26	8	50	6	42	M5	50	30	φ5.5	37	20	150
TBR20S	68	31	10	55	8	51	M6	54	37	φ5.5	40	20	150
TBR25S	82	41	12	65	10	65	M8	65	50	φ6.6	45	25	200
TBR30S	91	48	12	75	12	75	M8	75	60	φ6.6	55	25	200

Designation	Shaft Diameter	额定负荷 Basic load rating		尺寸 Dimensions (mm)										配合直线轴承	
		动负荷 Dynamic C N	Static Co N	W	G	A	M	S <sub>1</sub>	J	K	E	h <sub>2</sub>	型号 Designation	Basic load rating	
														Dynamic C N	静负荷 Static Co N
TBR16LUU	16	780	980	62	26	8	85	M5	50	60	31	18	2×LM16UUOP	392	490
TBR20LUU	20	1,568	2,352	68	31	10	96	M6	54	70	34	21	2×LM20UUOP	784	1,176
TBR25LUU	25	3,136	4,704	82	41	12	130	M8	65	100	41	28	2×LM25UUOP	1,568	2,352
TBR30LUU	30	3,528	5,880	91	48	12	140	M8	75	110	45.5	33.5	2×LM30UUOP	1,764	2,940