




JFB标准轴承套尺寸

JFB BEARING



d	D	dE7	Dr6	F	L												
					T _{-0.1} ⁰	15	20	25	30	35	40	50	60	80	100		
10	14	10	14	22	2	●	●										
12	18	12	18	25	3	●	●										
13	19	13	19	26		●	●										
14	20	14	20	27		●	●										
15	21	15	21	28		●	●	●	●								
16	22	16	22	29		●	●	●	●								
20	30	20	30	40		5	●	●	●	●		●					
25	35	25	35	45			●	●	●	●	●	●					
30	40	30	40	50			●	●	●	●	●	●					
32	40	32	40	50			●			●							
35	45	35	45	60			●		●		●	●					
40	50	40	50	65			●		●		●	●					
45	55	45	55	70					●		●	●	●				
50	60	50	60	75					●		●	●	●				
55	65	55	65	80							●		●				
60	75	60	75	90	7.5							●	●			●	
63	75	63	75	85												●	
70	85	70	85	105									●			●	
75	90	75	90	110										●			
80	100	80	100	120	10									●	●	●	
90	110	90	110	130										●	●		
100	120	100	120	150											●	●	●
120	140	120	140	170												●	●