

2. ヨドフロンの PFAチューブ

Yodoflon PFA tube

(単位/Units:mm,m,%)

品番 Product code	一般呼称 Nominal dimensions 外径×内径 Outer diameter x inner diameter	外径 Outer diameter	肉厚 Wall thickness	長さ (m) Length (m)	許容差 Tolerance			
					外径 Outer diameter	肉厚 Wall thickness	長さ Length	
7000	(ミリ サイズ) (Millimeter size)						-0 ~ +2.0%	
	3.0 × 2.0	3.0	0.5	10	±0.10	±0.08		
	4.0 × 2.0	4.0	1.0	50		±0.10		
	4.0 × 3.0	4.0	0.5	100		±0.08		
	6.0 × 4.0	6.0	1.0			±0.10		
	8.0 × 6.0	8.0	1.0					
	10.0 × 8.0	10.0	1.0		±0.13			
	12.0 × 10.0	12.0	1.0			±0.15		
	14.0 × 12.0	14.0	1.0		±0.15			
	19.0 × 16.0	19.0	1.5		±0.18			
	25.0 × 22.0	25.0	1.5		±0.20			
	(インチ サイズ) (Inch size)							
	6.35 × 3.95	6.4	1.20		±0.10	±0.12		
	6.35 × 4.35	6.4	1.00			±0.10		
	9.53 × 6.33	9.5	1.60		±0.12	±0.15		
	12.70 × 9.50	12.7	1.60		±0.15			
	19.00 × 15.80	19.0	1.60		±0.18			
	25.40 × 22.20	25.4	1.60		±0.20			

(注) 上記以外のサイズおよび7200(半導体用)、7300(低透過用)品種の生産もご相談に応じます。

Note: We will consider the production of Yodoflon tubes in sizes other than those shown above, and of 7200,7300 varieties of tubes.

3. ヨドフロンの FEPチューブ

Yodoflon FEP tube

(単位/Units:mm,m,%)

品番 Product code	一般呼称 Nominal dimensions 外径×内径 Outer diameter x inner diameter	外径 Outer diameter	肉厚 Wall thickness	長さ (m) Length (m)	許容差 Tolerance		
					外径 Outer diameter	肉厚 Wall thickness	長さ Length
6000	(ミリ サイズ) (Millimeter size)						-0 ~ +2.0%
	3.0 × 2.0	3.0	0.5	10	±0.10	±0.08	
	4.0 × 2.0	4.0	1.0	50		±0.10	
	4.0 × 3.0	4.0	0.5	100		±0.08	
	6.0 × 4.0	6.0	1.0			±0.10	
	8.0 × 6.0	8.0	1.0				
	10.0 × 8.0	10.0	1.0		±0.13		
	12.0 × 10.0	12.0	1.0			±0.15	
	14.0 × 12.0	14.0	1.0		±0.15		
	16.0 × 14.0	16.0	1.0		±0.18		
	24.0 × 20.0	24.0	2.0		±0.20	±0.15	
	30.0 × 26.0	30.0	2.0			±0.20	

(注) 上記以外のサイズの生産もご相談に応じます。

Note: We will consider the production of Yodoflon tube in sizes other than those shown above.