



白継手・黒継手 ラインナップ一覧表

アイテム サイズ	エルボ	45° エルボ	ストリート エルボ	チーズ	クロス	キャップ	ソケット	組フランジ	プラグ	ユニオン	角ニップル	ロックナット	サービス チーズ
	L	45L	SL	T	BCR	BCA	S	F2	P	U	NI	LN	ST
6	●		●	●※	●	●	●		●		●		
8	●	●	●	●	●	●	●		●	●	●	○	
10	●	●	●	●	●	●	●	●	●	●	●	○	
15	●	●	●	●	●	●	●	●	●	●	●	○	○
20	●	●	●	●	●	●	●	●	●	●	●	●	○
25	●	●	●	●	●	●	●	●	●	●	●	●	○
32	●	●	●	●	●	●	●	●	●	●	●	●	○
40	●	●	●	●	●	●	●	●	●	●	●	●	○
50	●	●	●	●	●	●	●	●	●	●	●	●	○
65	●	●	●	●	●	●	●	●	●	●	●	●	
80	●	●	●	●	●	●	●	●	●	●	●	○	
100	●	●	●	●	●	●	●	●	●	●	●	○	
125	●	●		●		●	●	●	●	●	●		
150	●	●		●		●	●	●	●	●	●		

アイテム サイズ	径違い エルボ	径違い チーズ	径違い ソケット	プッシング	径違い ニップル	径違い SL
	RL	RT	RS	BU	RNI	RSL
8×6	●※	●※	●※	●		
10×6	○※	●※	○※	●		
10×8	●	●	●	●	○	
15×6				○		
15×8	●	●	●	●	○	
15×10	●	●	●	●	○	○
20×6				●		
20×8	●	●	●	●		
20×10	●	●	●	●	○	
20×15	●	●	●	●	○	○
25×8		●	●	●		
25×10	●	●	●	●		
25×15	●	●	●	●	○	
25×20	●	●	●	●	○	○
32×10		●	●	●		
32×15	●	●	●	●		
32×20	●	●	●	●	○	○
32×25	●	●	●	●	○	○
40×10		●	●	●		
40×15	●	●	●	●		
40×20	●	●	●	●	○	
40×25	●	●	●	●	○	
40×32	●	●	●	●	○	○
50×10		●	●	●		
50×15	●	●	●	●		
50×20	●	●	●	●		
50×25	●	●	●	●	○	
50×32	●	●	●	●	○	
50×40	●	●	●	●	○	
65×15	●	●	●	●		
65×20	●	●	●	●		
65×25	●	●	●	●		
65×32	●	●	●	●		
65×40	●	●	●	●		
65×50	●	●	●	●		

アイテム サイズ	径違い エルボ	径違い チーズ	径違い ソケット	プッシング
	RL	RT	RS	BU
80×15	●	●	●	●
80×20	●	●	●	●
80×25	●	●	●	●
80×32	●	●	●	●
80×40	●	●	●	●
80×50	●	●	●	●
80×65	●	●	●	●
100×15		●		
100×20	●	●	●	●
100×25	●	●	●	●
100×32	●	●	●	●
100×40	●	●	●	●
100×50	●	●	●	●
100×65	●	●	●	●
100×80	●	●	●	●
125×40		●		
125×50		●	●	●
125×65	●	●	●	●
125×80	●	●	●	●
125×100	●	●	●	●
150×25				●
150×32				●
150×40				●
150×50		●	●	●
150×65	●	●	●	●
150×80	●	●	●	●
150×100	●	●	●	●
150×125	●	●	●	●

●・・・白継手・黒継手ともに製作品種
 ○・・・白継手のみ製作品種
 ※・・・バンド付