



異径両口 リングジョイント



C3604BD



| 品番 | 適用管外径 | | 寸法 (mm) | | | | | |
|---------|-----------|-----------|---------|----|----|-------|-------|------|
| | ϕ D1 | ϕ D2 | B | B1 | B2 | d1 | d2 | L(約) |
| RE-0602 | 6 | 6.35 | 14 | 17 | 17 | PF1/4 | PF1/4 | 40 |
| RE-0608 | 6 | 8 | 14 | 17 | 17 | PF1/4 | PF1/4 | 41 |
| RE-0603 | 6 | 9.53 | 17 | 17 | 21 | PF1/4 | PF3/8 | 43 |
| RE-0610 | 6 | 10 | 17 | 17 | 21 | PF1/4 | PF3/8 | 43 |
| RE-0208 | 6.35 | 8 | 14 | 17 | 17 | PF1/4 | PF1/4 | 41 |
| RE-0203 | 6.35 | 9.53 | 17 | 17 | 21 | PF1/4 | PF3/8 | 43 |
| RE-0210 | 6.35 | 10 | 17 | 17 | 21 | PF1/4 | PF3/8 | 43 |
| RE-0803 | 8 | 9.53 | 17 | 17 | 21 | PF1/4 | PF3/8 | 44 |
| RE-0810 | 8 | 10 | 17 | 17 | 21 | PF1/4 | PF3/8 | 44 |
| RE-0310 | 9.53 | 10 | 17 | 21 | 21 | PF3/8 | PF3/8 | 45 |
| RE-0312 | 9.53 | 12 | 22 | 21 | 24 | PF3/8 | PF1/2 | 51 |
| RE-0304 | 9.53 | 12.7 | 22 | 21 | 24 | PF3/8 | PF1/2 | 52 |
| RE-0315 | 9.53 | 15 | 24 | 21 | 27 | PF3/8 | PF5/8 | 51 |
| RE-0305 | 9.53 | 15.88 | 24 | 21 | 27 | PF3/8 | PF5/8 | 52 |
| RE-1012 | 10 | 12 | 22 | 21 | 24 | PF3/8 | PF1/2 | 51 |
| RE-1004 | 10 | 12.7 | 22 | 21 | 24 | PF3/8 | PF1/2 | 52 |
| RE-1015 | 10 | 15 | 24 | 21 | 27 | PF3/8 | PF5/8 | 52 |
| RE-1005 | 10 | 15.88 | 24 | 21 | 27 | PF3/8 | PF5/8 | 53 |
| RE-1204 | 12 | 12.7 | 22 | 24 | 24 | PF1/2 | PF1/2 | 56 |
| RE-1215 | 12 | 15 | 24 | 24 | 27 | PF1/2 | PF5/8 | 56 |
| RE-1205 | 12 | 15.88 | 24 | 24 | 27 | PF1/2 | PF5/8 | 57 |
| RE-0415 | 12.7 | 15 | 24 | 24 | 27 | PF1/2 | PF5/8 | 57 |
| RE-0405 | 12.7 | 15.88 | 24 | 24 | 27 | PF1/2 | PF5/8 | 58 |

両口ロックナット付 リングジョイント


C3604BD



| 品番 | 適用管外径 | 寸法 (mm) | | | | |
|---------|----------|---------|----|----|-------|------|
| | ϕ D | B | B1 | B2 | d | L(約) |
| RW-2206 | 6 | 17 | 17 | 17 | PF1/4 | 52 |
| RW-2202 | 6.35 | 17 | 17 | 17 | PF1/4 | 52 |
| RW-2208 | 8 | 17 | 17 | 17 | PF1/4 | 53 |
| RW-2303 | 9.53 | 19 | 21 | 19 | PF3/8 | 59 |
| RW-2310 | 10 | 19 | 21 | 19 | PF3/8 | 60 |
| RW-2412 | 12 | 23 | 24 | 23 | PF1/2 | 73 |
| RW-2404 | 12.7 | 23 | 24 | 23 | PF1/2 | 74 |

ロックナット

C3604BD



| 品番 | 寸法 (mm) | | |
|---------|---------|----|---|
| | d | B | T |
| NR-1001 | PF1/8 | 15 | 4 |
| NR-1002 | PF1/4 | 17 | 5 |
| NR-1003 | PF3/8 | 19 | 5 |
| NR-1004 | PF1/2 | 23 | 6 |
| NR-1006 | PF3/4 | 30 | 7 |