



## Accessories

| Ordering data                                                                       |                            | Code                                                                                  | Valve function | Part No. | Type            |
|-------------------------------------------------------------------------------------|----------------------------|---------------------------------------------------------------------------------------|----------------|----------|-----------------|
| <b>Individual solenoid valve – width 20 mm</b>                                      |                            |                                                                                       |                |          |                 |
|    | <b>5/2-way valve</b>       |                                                                                       |                |          |                 |
|                                                                                     | Position function 1-32: M  | Single solenoid                                                                       |                | 537952   | VMPA2-M1H-M-PI  |
|                                                                                     | Position function 1-32: MS | Single solenoid, mechanical spring return                                             |                | 571333   | VMPA2-M1H-MS-PI |
|                                                                                     | Position function 1-32: J  | Double solenoid                                                                       |                | 537953   | VMPA2-M1H-J-PI  |
|                                                                                     | <b>2x 3/2-way valve</b>    |                                                                                       |                |          |                 |
|                                                                                     | Position function 1-32: N  | Normally open                                                                         |                | 537958   | VMPA2-M1H-N-PI  |
|                                                                                     | Position function 1-32: NS | Normally open,<br>Mechanical spring return                                            |                | 568655   | VMPA2-M1H-NS-PI |
|                                                                                     | Position function 1-32: K  | Normally closed                                                                       |                | 537957   | VMPA2-M1H-K-PI  |
|                                                                                     | Position function 1-32: KS | Normally closed,<br>Mechanical spring return                                          |                | 568656   | VMPA2-M1H-KS-PI |
|                                                                                     | Position function 1-32: H  | 1x normally open, 1x normally closed                                                  |                | 537959   | VMPA2-M1H-H-PI  |
|                                                                                     | Position function 1-32: HS | 1x normally open, 1x normally closed,<br>Mechanical spring return                     |                | 568658   | VMPA2-M1H-HS-PI |
|                                                                                     | <b>5/3-way valve</b>       |                                                                                       |                |          |                 |
|                                                                                     | Position function 1-32: B  | Mid-position pressurised                                                              |                | 537954   | VMPA2-M1H-B-PI  |
|                                                                                     | Position function 1-32: G  | Mid-position closed                                                                   |                | 537955   | VMPA2-M1H-G-PI  |
|                                                                                     | Position function 1-32: E  | Mid-position exhausted                                                                |                | 537956   | VMPA2-M1H-E-PI  |
|                                                                                     | <b>1x 3/2-way valve</b>    |                                                                                       |                |          |                 |
|                                                                                     | Position function 1-32: W  | Normally open, external compressed air supply                                         |                | 540051   | VMPA2-M1H-W-PI  |
|                                                                                     | Position function 1-32: X  | Normally closed, external compressed air supply                                       |                | 537961   | VMPA2-M1H-X-PI  |
|                                                                                     | <b>2x 2/2-way valve</b>    |                                                                                       |                |          |                 |
|                                                                                     | Position function 1-32: D  | Normally closed                                                                       |                | 537960   | VMPA2-M1H-D-PI  |
|                                                                                     | Position function 1-32: DS | Normally closed,<br>Mechanical spring return                                          |                | 568657   | VMPA2-M1H-DS-PI |
|                                                                                     | Position function 1-32: I  | 1x normally closed,<br>1x normally closed, reversible only                            |                | 543703   | VMPA2-M1H-I-PI  |
| <b>Vacant position – Installation width 20 mm</b>                                   |                            |                                                                                       |                |          |                 |
|  | Position function 1-32: L  | Cover plate for a valve position in width 20 mm<br>A self-adhesive label is supplied. |                | 537962   | VMPA2-RP        |