

Key Selector Switches

Package Quantity: 1

Shape	Position	Operation	Key Retained at ●	Contact	Part No.	
					IP40	IP65
Rectangular AS6H 	90° 2-position	Maintained	A 	SPDT	AS6H-2KT1AC	AS6H-2KT1PAC
				DPDT	AS6H-2KT2AC	AS6H-2KT2PAC
			B 	SPDT	AS6H-2KT1BC	AS6H-2KT1PBC
				DPDT	AS6H-2KT2BC	AS6H-2KT2PBC
		Spring return from right	C 	SPDT	AS6H-2KT1CC	AS6H-2KT1PCC
				DPDT	AS6H-2KT2CC	AS6H-2KT2PCC
	45° 3-position	Maintained	B 	SPDT	AS6H-21KT1BC	AS6H-21KT1PBC
				DPDT	AS6H-21KT2BC	AS6H-21KT2PBC
			A 	DPDT	AS6H-3KT2AC	AS6H-3KT2PAC
			B 	DPDT	AS6H-3KT2BC	AS6H-3KT2PBC
			C 	DPDT	AS6H-3KT2CC	AS6H-3KT2PCC
			D 	DPDT	AS6H-3KT2DC	AS6H-3KT2PDC
		Spring return from right	E 	DPDT	AS6H-3KT2EC	AS6H-3KT2PEC
			G 	DPDT	AS6H-3KT2GC	AS6H-3KT2PGC
			H 	DPDT	AS6H-3KT2HC	AS6H-3KT2PHC
		Spring return from left	B 	DPDT	AS6H-31KT2BC	AS6H-31KT2PBC
			D 	DPDT	AS6H-31KT2DC	AS6H-31KT2PDC
			G 	DPDT	AS6H-31KT2GC	AS6H-31KT2PGC
		Spring return two-way	C 	DPDT	AS6H-32KT2CC	AS6H-32KT2PCC
			D 	DPDT	AS6H-32KT2DC	AS6H-32KT2PDC
			H 	DPDT	AS6H-32KT2HC	AS6H-32KT2PHC
			D 	DPDT	AS6H-33KT2DC	AS6H-33KT2PDC

- Key is retained at ● positions and removable at ○ positions.
- Two keys are supplied.
- The front of key cylinder is made of metal.
- Only one type of key is available.

APEM

Switches & Pilot Lights

Control Boxes

Emergency Stop Switches

Enabling Switches

Safety Products

Explosion Proof

Terminal Blocks

Relays & Sockets

Circuit Protectors

Power Supplies

LED Illumination

Controllers

Operator Interfaces

Sensors

AUTO-ID

Flush Silhouette

ø16

ø22

ø30

Miniature

Pilot Lights

LB

A6

Contact Operation

Operator Position & Contact Operation (Top View)					
Positions		Contact	Left	Center	Right
90° 2-position	 Maintained  Spring return from right	SPDT		—	
		DPDT		—	
45° 3-position	 Maintained  Spring return from right  Spring return from left  Spring return two-way	DPDT			



Download catalogs and CAD from <http://asia.idec.com/downloads>