



## EPIC® H-D 1.6 stamped contacts

For inserts and modules of the EPIC® rectangular connectors



### Info

- Choice of high quality gold or silver plated contacts
- 2 crimp areas for wire and insulation crimp

### Suitable tools

- Pneumatic crimping machine for single contacts
- Crimping tool for single contacts

- Crimping dies for single contacts
- Locator
- Removal tool

### Technical data



ETIM 5.0 Class-ID: EC000796  
ETIM 5.0 Class-Description:  
Contact for industrial connectors

Article number	Article description	Contact type	Conductor cross-section (mm <sup>2</sup> )	Surface	Stripping length (mm)	Pieces / PU
<b>Contacts</b>						
11241100	H-D 1.6 stamped	male	0.14 - 0.50	Ag	2.5 + 0.5	100
11231100	H-D 1.6 stamped	female	0.14 - 0.50	Ag	2.5 + 0.5	100
11221000	H-D 1.6 stamped	male	0.50 - 1.50	Ag	3.5 + 0.5	100
11236100	H-D 1.6 stamped	female	0.50 - 1.50	Ag	3.5 + 0.5	100
11223500	H-D 1.6 stamped	male	1.50 - 2.50	Ag	3.5 + 0.5	100
11228500	H-D 1.6 stamped	female	1.50 - 2.50	Ag	3.5 + 0.5	100
11243100	H-D 1.6 stamped	male	0.14 - 0.50	Au	2.5 + 0.5	100
11233100	H-D 1.6 stamped	female	0.14 - 0.50	Au	2.5 + 0.5	100
11221300	H-D 1.6 stamped	male	0.50 - 1.50	Au	3.5 + 0.5	100
11238100	H-D 1.6 stamped	female	0.50 - 1.50	Au	3.5 + 0.5	100

Photographs are not to scale and do not represent detailed images of the respective products.

## EPIC® Tools for contacts H-D 1.6 stamped

For inserts and modules of the EPIC® rectangular connectors



### Product features

- Locator and crimping dies fit together with the crimping tool 11147000 and the crimping machine 11147001

Article number	Article description	Version	Note	Pieces / PU
<b>Tools</b>				
11147000	Crimping tool	In tool case	without crimping dies, without locator	1
11147001	Crimping machine	Pneumatic, 5 - 10 bar	without crimping dies, without locator	1
11147170	Crimping dies	For crimping tools	For contacts: H-D 1.6 stamped (0.14 - 0.5 mm <sup>2</sup> )	1
11147180	Crimping dies	11147000, 11147001 For crimping tools	For contacts: H-D 1.6 stamped (0.5 - 1.5 mm <sup>2</sup> ), MC 2.5 stamped (0.5 - 1.5 mm <sup>2</sup> )	1
11147190	Crimping dies	11147000, 11147001 For crimping tools	For contacts: H-D 1.6 stamped (1.5 - 2.5 mm <sup>2</sup> ), MC 2.5 stamped (1.5 - 2.5 mm <sup>2</sup> )	1
11147300	Locator		For contacts: H-D 1.6 machined, H-D 1.6 stamped	1
11161000	Removal tool		For contacts: H-D 1.6 machined, H-D 1.6 stamped	1

Photographs are not to scale and do not represent detailed images of the respective products.