


SNSS-RY Socket Head Cap Screws - Low Temperature Black Chrome




WEB Selection Tool
 WEB CAD Download
 Seizing Prevention
 Chemical-proof
 Antireflection
 SUS Stainless steel



- Tightening property (reference)
Part Number : SNSS-M5 - 25-RY

➔ P.663



- Excellent corrosion resistance, chemical resistance, and abrasion resistance.
- Due to low outgas, screws can be used under vacuum environments.
- The coating has excellent lubricating ability and is suitable for prevention of seizing.
- Spectral reflectance is 1.5% or less. These screws are intended for optical instruments and other applications that require antireflection. ➔ P.663

● Application

Seizing prevention and reflection resistance, Optical instruments, FPD production equipment, and semiconductor devices

● Material/Finish



	SNSS-RY
Main Body	SUSXM7 (S.S. Grade : A2) Low Temperature Black Chrome Treatment*
Strength Class	A2-70

*The surface treatment for **SNSS-RY** has been changed to low temperature black chrome treatment.

● Part number specification

SNSS-M5-16-RY

Product Code **1** **2** Product Code

Part Number	M	L											D1	L1	B	Mass (g)
			1	2	3	4	5	6	7	8	9	10				
SNSS-M3-RY	M3	5	6	8	10	12	16	20					5.5	3	2.5	0.67 - 1.4
SNSS-M4-RY	M4		6	8	10	12	16	20	25				7	4	3	1.5 - 3.2
SNSS-M5-RY	M5			8	10	12	16	20	25				8.5	5	4	2.5 - 4.8
SNSS-M6-RY	M6				10	12	16	20	25	30			10	6	5	4.7 - 8.3
SNSS-M8-RY	M8						16	20	25	30	35		13	8	6	12 - 19
SNSS-M10-RY	M10							20	25	30	35	40	16	10	8	23 - 33

Part Number	Qty per pack
SNSS-M3-RY	1
SNSS-M4-RY	1
SNSS-M5-RY	1
SNSS-M6-RY	1
SNSS-M8-RY	1
SNSS-M10-RY	1

Individual Sales ➔ P.794
 Cleanroom Wash & Packaging ➔ P.792
 Screw Length Adjustment ➔ P.796
 Vibration Resistant ➔ P.795
 Modification process for captive use ➔ P.791

1 unit in 1 bag Available / Add'l charge Not Available Not Available Not Available

Special Screws
 Vacuum Application
 Low Profile, Small Head
 High Performance S.S.
 Titanium
 Special Material
 Chemical Resistance
 Special Surface Treatment
 Miniature
 Captive/Full Thread
 Functional
 Inch
 Tamper Resistance
 Hexabolular Socket Head
 Plugs
 Plastic
 Washers/Lock Nuts