

Compact enclosures AE



System accessories Page 613 AE stainless steel Page 219 Hygienic Design Page 208

Material:

- Enclosure: Sheet steel
- Door: Sheet steel, all-round foamed-in PU seal

Surface finish:

- Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint
- Mounting plate: Zinc-plated

Colour:


- RAL 7035

Supply includes:

- Enclosure with hinged door(s), of all-round solid construction
 - Gland plate(s) in enclosure base
 - Mounting plate
 - Lock: 3 mm double-bit
- Please observe the product-specific scope of supply.

Approvals:

- UL
- cUL
- CSA
- TÜV
- Germanischer Lloyd
- Russian Maritime Register of Shipping
- Lloyds Register of Shipping
- Bureau Veritas



Width (B) mm	Packs of	200	200	300	300	300	Page
Height (H) mm		300	300	300	300	400	
Depth (T) mm		120	155	155	210	210	
Mounting plate width (F) mm		162	162	254	254	254	
Mounting plate height (G) mm		275	275	275	275	375	
Material thickness - enclosure mm		1.25	1.25	1.38	1.38	1.38	
Material thickness - door mm		1.5	1.5	1.5	1.5	1.5	
Mounting plate thickness mm		2.0	2.0	2.0	2.0	2.0	
Model No.	1 pc(s).	1032.500	1035.500	1036.500	1033.500	1034.500	
Weight kg		4.0	4.5	6.1	7.0	8.8	
Protection category IP to IEC 60 529		IP 55	IP 55	IP 66	IP 66	IP 66	
Protection category NEMA		NEMA 12	NEMA 12	NEMA 4	NEMA 4	NEMA 4	
Product-specific scope of supply							
Door(s)		1	1	1	1	1	
Door hinged on the right, may be swapped to the left		-	-	■	■	■	
Cam lock		1	1	1	1	1	
Gland plate, size		1	1	-	-	-	
Gland plate, qty.		1	1	1	1	1	
Accessories							
Rails for interior installation	4 pc(s).	-	-	-	2383.210	2383.210	716
Wall mounting bracket	4 pc(s).	2508.100	2508.100	2508.100	2508.100	2508.100	698
Baying kit	1 pc(s).	1199.100	1199.100	1199.100	1199.100	1199.100	658
180° hinges	2 pc(s).	2449.000	2449.000	2449.000	2449.000	2449.000	684
Door stay	5 pc(s).	-	-	2519.000	2519.000	2519.000	688
Eyebolts		-	-	-	-	-	
LED system light		-	-	-	-	-	
Dust guard trim	1 pc(s).	2426.500	2426.500	2426.500	2426.500	2426.500	691
Wiring plan pocket, plastic		see page	see page	see page	see page	see page	687
Cable gland, brass		see page	see page	see page	see page	see page	776
Cable gland, polyamide		see page	see page	see page	see page	see page	776
Mounting bars		-	-	-	-	-	
Earth straps		see page	see page	see page	see page	see page	762