

The number next to the logo mark indicates items in stock for each brand.

Door Closers

Door Stoppers

Hinges

Slide Bolt Latches

Catches

Handles

Keys

Chains

Wire Ropes

Metal Fittings for Handling

Suspension Metal Fittings

Shelf Peg Metal Fittings

Joint Fittings

Steel Wires

Wire Nets

Inspection Doors, Air Inlet/Outlets

Handrails, Slopes

Corrugated Plates

Plastic Materials

Metal Materials

Construction Materials

Sash Rollers

Door Hangers

TRUSCO



Stock 38,650 Items

Pelican S Hook




- Features • It is designed that one side of hooks opens more deeply.
 Use • For edge brackets of a load handling rope, etc.
 Materials • **Stainless Steel (SUS304)**
 Origin • China

Example



TPS-5



Order Unit: 1 Piece

(Price revision date: Jan, 2017) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	L1 (mm)	L2 (mm)	W1 (mm)	W2 (mm)	S (mm)	R (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
300-8878	TPS-5	¥ 314	¥ 340	5	50	40	8.5	10.0	5.0	4.0	0.20	20	16
300-8886	TPS-6	¥ 528	¥ 570	6	60	48	12.0	11.5	6.0	5.5	0.29	20	29
300-8894	TPS-8	¥ 703	¥ 760	8	76	60	15.0	16.0	8.0	7.5	0.49	20	69
300-8908	TPS-10	¥ 1,083	¥ 1,170	10	100	80	17.5	20.0	9.5	9.0	0.98	20	132
300-8916	TPS-12	¥ 1,296	¥ 1,400	12	120	96	22.0	22.0	10.0	10.0	1.47	20	223

Contact us: 0120-509-849 <http://www.orange-book.com/>

MIZUMOTO MACHINE



Stock 529 Items


S Hook SA Type



- Features • S hook with thin diameter.
 Use • For hanging brackets of storage for general items such as tools, equipment, etc.
 Materials • **Stainless Steel (SUS304)**
 Origin • China



B-1249



Order Unit: 1 Bag

(Price revision date: Jan, 2016) MIZUMOTO MACHINE MFG.Co.Ltd

Order Code	Item No.	Price (per bag)	MSRP (per bag)	D (mm)	L1 (mm)	L2 (mm)	W1 (mm)	W2 (mm)	S1 (mm)	S2 (mm)	Working Load (kN)	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
378-8288	B-1249	¥ 162	¥ 190	2.3	36.6	32	12	12	7.5	8	0.05	2	30	4
378-8199	B-1149	¥ 162	¥ 190	2.5	35.0	30	10	13	7.0	-	0.05	2	30	6

Contact us: 079-246-2501 <http://www.mizumoto-mm.co.jp/>

MIZUMOTO MACHINE



Stock 529 Items


Wire Hook



- Features • Stainless steel less rusty and excellent in durability.
 Use • For connection brackets of a belt, etc.
 • For joint of edge brackets.
 Materials • **Stainless Steel (SUS304)**
 Origin • China



B-2496



Order Unit: 1 Piece

MIZUMOTO MACHINE MFG.Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	L (mm)	W (mm)	H (mm)	R (mm)	Handing load (N/kgf)	SPQ (piece)	Weight (g)
833-7813	B-2496	¥ 832	¥ 980	7	55	26	35	7	784/80	10	65
833-7814	B-2497	¥ 917	¥ 1,080	7	71	26	35	7	784/80	10	75
833-7815	B-2498	¥ 917	¥ 1,080	7	55	46	35	7	686/70	10	75
833-7825	B-2531	¥ 2,105	¥ 2,480	10	100	46	40	10	1470/150	10	215

Contact us: 079-246-2501 <http://www.mizumoto-mm.co.jp/>

MIZUMOTO MACHINE



Stock 529 Items


Wire Hook



- Features • Stainless steel less rusty and excellent in durability.
 Use • For connection brackets of a belt, etc.
 • For joint of edge brackets.
 Materials • **Stainless Steel (SUS304)**
 Origin • China



B-2499



Order Unit: 1 Piece

MIZUMOTO MACHINE MFG.Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	L (mm)	W (mm)	H (mm)	H2 (mm)	R (mm)	R2 (mm)	Handing load (N/kgf)	SPQ (piece)	Weight (g)
833-7816	B-2499	¥ 1,171	¥ 1,380	7	65	27	48	22	12.5	5	490/50	10	97
833-7817	B-2500	¥ 1,476	¥ 1,740	7	65	47	48	22	12.5	5	441/45	10	107

Contact us: 079-246-2501 <http://www.mizumoto-mm.co.jp/>