

Replacement Blade for Handsaws

Stock 39 Items

5-843


Prices displayed include 8% tax.

For Saw Main Bodies, see p. 4-1146 to 1148

Cutting Supplies

TRUSCO **Stock 38,650 Items**

Replacement Blade for Handsaws



Estimated Unit Price per Sheet
¥204

Estimated Unit Price per Sheet
¥197

- Features** • Low price bimetal high-speed handsaw.
Use • For iron working, stainless pipes and piping/for cutting electrical pipe work.
Materials • Blade Edge: Bimetal High-Speed Steel • Saw Blade: Spring Steel **Origin** • Taiwan



250mm width Specs • Compatible Model: 250mm wide Hacksaw

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Number of Ridges	Nominal Dimension (mm)	Total Length (mm)	Thickness (mm)	Q'ty Per Bag (sheet)	Weight (g/bag)
389-5220	THS25018-5P	¥1,018	¥1,100	18	250	263	0.65	5	80
389-5238	THS25024-5P	¥1,018	¥1,100	24	250	263	0.65	5	80
389-5246	THS25032-5P	¥1,018	¥1,100	32	250	263	0.65	5	80

300mm width Specs • Compatible Model: 300mm wide Hacksaw

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Number of Ridges	Nominal Dimension (mm)	Total Length (mm)	Thickness (mm)	Q'ty Per Bag (sheet)	SPQ (bag)	Weight (g/bag)
445-5835	THS30018-5P	¥982	¥1,060	18	300	313	0.65	5	8	90
445-5843	THS30024-5P	¥982	¥1,060	24	300	313	0.65	5	8	90
445-5851	THS30032-5P	¥982	¥1,060	32	300	313	0.65	5	8	90

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

Replacement Blade for Handsaws



Estimated Unit Price per Sheet
¥229

Estimated Unit Price per Sheet
¥227

- Features** • Common use 100% high speed steel handsaw.
 • More resilient than traditional high-speed steel saw blades, making it hard to break.
Use • For iron working, pipes such as stainless pipes/for cutting electrical pipe work.
Specs • Compatible Model: 250mm wide Hacksaw
Materials • Blade Edge/Saw Body: All High Speed Steel HSS
Origin • China

Including 5 pieces

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Number of Ridges	Nominal Dimension (mm)	Total Length (mm)	Thickness (mm)	Q'ty Per Bag (sheet)	Weight (g/bag)
232-0258	NS3805-250-24-5P	¥1,143	¥1,410	24	250	263	0.65	5	80

100 Pieces

Order Unit: 1 Box

Order Code	Item No.	Price (per box)	MSRP (per box)	Number of Ridges	Nominal Dimension (mm)	Total Length (mm)	Thickness (mm)	Q'ty Per Box (sheet)	Weight (kg/box)
232-0185	NS3805-250-24-100P	¥22,680	¥28,000	24	250	263	0.65	100	1.7

Contact us:0120-509-849 <http://www.orange-book.com/>

KAKURI **Stock 115 Items**

Metal Cutting Saw



14146 (for slates)

- Features** • Efficient work with the coarse blade for thick items and a fine blade for thinner items and pipes.
 • Compatible with 250mm hacksaws for metal working.
Specs • Compatible Model: 250mm wide Hacksaw
Origin • Japan

Estimated Unit Price per Sheet
¥67 to ¥705

Order Unit: 1 Bag (Price revision date: Jan, 2018) KAKURI Corporation

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Number of Ridges	Nominal Dimension (mm)	Total Length (mm)	Thickness (mm)	Use	Materials	Q'ty Per Bag (sheet)	Weight (g/bag)
753-6151	14146	¥341	¥350	10	250	265	0.6	For Slates	SK-3	3	50
753-6160	14147	¥201	¥200	24	250	265	0.7	For Aluminum, Copper, Brass	SK Material	3	50
753-6178	14148	¥341	¥350	18	250	265	0.6	For Aluminum, Copper, Brass	SK-3 Flex	3	50
753-6186	14149	¥583	¥600	18	250	265	0.6	For Aluminum, Copper, Brass	SKS-7	3	50
753-6194	14150	¥341	¥350	24	250	265	0.6	For Standard Metal Materials, Round Bars, Angles	SK-3	3	50
753-6208	14151	¥341	¥350	24	250	265	0.6	For Standard Metal Materials, Round Bars, Angles	SK-3 Flex	3	50
753-6216	14152	¥583	¥600	24	250	265	0.6	For Standard Metal Materials, Round Bars, Angles	SKS-7	3	50
753-6224	14153	¥341	¥350	32	250	265	0.6	For Thin Iron Sheets and Pipes	SK-3 Flex	3	50
753-6232	14154	¥583	¥600	32	250	265	0.6	For Thin Iron Sheets and Pipes	SKS-7	3	50
753-6241	14155	¥1,166	¥1,200	24	250	265	0.6	For Stainless Steel	HSS	2	35
753-6259	14156	¥1,166	¥1,200	32	250	265	0.7	For Stainless Steel	HSS	2	35
753-6267	14157	¥1,410	¥1,450	24	250	265	0.7	Universal Type	PW/HSS Bimetal	2	35

Contact us:0256-34-6113 <http://www.kakuri.co.jp/>

Please wear protective equipment to use safely.