


WPBエスリーブ



WPBエスリーブ寸法表

単位：mm

呼び番号 標準(PN 104)	エスリーブおよびみぞ寸法												運用パッキン
	D	d	H	t	D ₁	D ₂	D ₃	G	B	A	E	W	
WPB- 40A	40	30	14	1.5	39	36	38	8.5	1.8	7	10.6	27.6	SKY- 30
WPB- 45A	45	35	15	1.5	44	41	43	8.5	1.8	8	11.6	28.6	SKY- 35
WPB- 50A	50	40	15	1.5	49	46	48	8.5	1.8	8	11.6	28.6	SKY- 40
WPB- 55A	55	45	16	2	54	51	53	9	1.8	8	11.6	29.6	SKY- 45
WPB- 60A	60	50	16	2	59	56	58	9	1.8	8	11.6	29.6	SKY- 50
WPB- 63A	63	53	17	2	62	59	61	9	1.8	9	12.6	30.6	SKY- 53
WPB- 65	65	55	17	2	64	61	63	9	1.8	9	12.6	30.6	SKY- 55
WPB- 70	70	60	18	2	69	66	68	9	1.8	10	13.6	31.6	SKY- 60
WPB- 71	71	60	18	2	70	67	69	10	1.8	10	13.6	33.6	SKY- 60A
WPB- 75	75	65	20	2	74	71	73	9	1.8	12	15.6	33.6	SKY- 65
WPB- 80	80	71	20	2	79	76	78	9	1.8	12	15.6	33.6	SKY- 71
WPB- 90	90	80	20	2	89	86	88	9	1.8	12	15.6	33.6	SKY- 80
WPB- 100	100	85	26	2	98	96	98	12	2.8	16	21.6	45.6	SKY- 85
WPB- 110	110	95	28	2	108	106	108	12	2.8	18	23.6	47.6	SKY- 95
WPB- 115	115	100	30	2	113	111	113	12	2.8	20	25.6	49.6	SKY- 100
WPB- 120	120	106	30	2	118	116	118	11.5	2.8	20	25.6	48.6	SKY- 106
WPB- 125	125	112	32	2	123	121	123	12	2.8	22	27.6	51.6	SKY- 112A
WPB- 140	140	125	36	2	138	134	138	12	2.8	26	31.6	55.6	SKY- 125
WPB- 150	150	136	39	3	148	144	148	12.5	2.8	27	32.6	57.6	SKY- 136
WPB- 160	160	145	42	3	158	154	158	13	2.8	30	35.6	61.6	SKY- 145
WPB- 180	180	165	46	3	178	174	178	13	2.8	34	39.6	65.6	SKY- 165

★ご注文・お問合せは、呼び番号にてご指示下さい。

★表中・呼び番号が色地のものは在庫しております。