




## Wheel Conveyors for Picking Rack


It is easy to disassemble and assemble, excellent in reuse and recyclability.

Example



- Features** •By assembly of frame and resin wheel unit, disassembly and assembly are easy, reuse and recyclability are excellent.  
**Use** •Wheel conveyor for flow rack and picking rack.  
**Specs** •Load Per Wheel: 10kg  
**Materials** •Frame: Electro-zinc Plated Chrome-Free Steel Plate  
 •Wheel: Polypropylene (PP) •End Cap: Polypropylene (PP)  
**Origin** •Japan

Basic Structure of V-3620ECON



### Item No. Example V - 18 20 ECON - 20 - 1000

Wheel Diameter	Wheel Width	Pitch	Conveyor Length
18=18mm 36=36mm	20mm	20=20mm 40=40mm 25=25mm 50=50mm	1000=1000mm 2400=2400mm 1800=1800mm 3000=3000mm 2000=2000mm



Stock 38,650 Items

### Wheel Conveyor for Cassette Type Picking Rack (wheel diameter 18mm)




Com Drawing



V-1820ECON

- Features** •Wheel made of resin is being used.  
 •By assembly of frame and resin wheel unit, disassembly and assembly are easy, reuse and recyclability are excellent.  
**Use** •Wheel conveyor for flow rack and picking rack.  
**Specs** •Load Per Wheel: 10kg  
**Materials** •Frame: Electro-zinc Plated Chrome-Free Steel Plate  
 •Wheel: Polypropylene (PP)  
 •End Cap: Polypropylene (PP)  
**Origin** •Japan



Order Unit: 1 Piece | Factory direct | No freight charge | Excluding remote islands |

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Wheel Diameter (mm)	Wheel Width (mm)	Pitch (mm)	Conveyor Length (mm)	SPQ (piece)	Weight (kg)
★461-1292	V-1820ECON-20-1000	¥2,610	¥2,820	18	20	20	1000	1	1.24
★461-1306	V-1820ECON-20-1800	¥4,712	¥5,090	18	20	20	1800	1	2.24
★461-1314	V-1820ECON-20-2000	¥5,221	¥5,640	18	20	20	2000	1	2.48
★461-1322	V-1820ECON-20-2400	¥6,267	¥6,770	18	20	20	2400	1	2.98
★461-1331	V-1820ECON-20-3000	¥7,831	¥8,460	18	20	20	3000	1	3.72
★461-1357	V-1820ECON-25-1000	¥2,323	¥2,510	18	20	25	1000	1	1.47
★461-1365	V-1820ECON-25-1800	¥4,194	¥4,530	18	20	25	1800	1	2.64
★461-1373	V-1820ECON-25-2000	¥4,638	¥5,010	18	20	25	2000	1	2.93
★461-1381	V-1820ECON-25-2400	¥5,573	¥6,020	18	20	25	2400	1	3.51
★461-1390	V-1820ECON-25-3000	¥6,952	¥7,510	18	20	25	3000	1	4.39

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock 38,650 Items

### Wheel Conveyor for Cassette Type Picking Rack (wheel diameter 36mm)




Com Drawing



V-3620ECON

- Features** •Wheel made of resin is being used.  
 •By assembly of frame and resin wheel unit, disassembly and assembly are easy, reuse and recyclability are excellent.  
**Use** •Wheel conveyor for flow rack and picking rack.  
**Specs** •Load Per Wheel: 10kg  
**Materials** •Frame: Electro-zinc Plated Chrome-Free Steel Plate  
 •Wheel: Polypropylene (PP)  
 •End Cap: Polypropylene (PP)  
**Origin** •Japan



Order Unit: 1 Piece | Factory direct | No freight charge | Excluding remote islands |

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Wheel Diameter (mm)	Wheel Width (mm)	Pitch (mm)	Conveyor Length (mm)	SPQ (piece)	Weight (kg)
★461-1969	V-3620ECON-40-1000	¥2,278	¥2,460	36	20	40	1000	1	1.20
★461-1977	V-3620ECON-40-1800	¥4,202	¥4,540	36	20	40	1800	1	2.16
★461-1985	V-3620ECON-40-2000	¥4,638	¥5,010	36	20	40	2000	1	2.40
★461-1993	V-3620ECON-40-2400	¥5,610	¥6,060	36	20	40	2400	1	2.88
★461-2001	V-3620ECON-40-3000	¥6,915	¥7,470	36	20	40	3000	1	3.60
★461-2027	V-3620ECON-50-1000	¥2,019	¥2,180	36	20	50	1000	1	1.16
★461-2035	V-3620ECON-50-1800	¥3,684	¥3,980	36	20	50	1800	1	2.09
★461-2043	V-3620ECON-50-2000	¥4,027	¥4,350	36	20	50	2000	1	2.32
★461-2051	V-3620ECON-50-2400	¥4,915	¥5,310	36	20	50	2400	1	2.79
★461-2060	V-3620ECON-50-3000	¥6,091	¥6,580	36	20	50	3000	1	3.48

Contact us:0120-509-849 <http://www.orange-book.com/>