



















検査スタンド —機械式精密型 / 油圧式精密型—

Universal Magnetic Stand

Mechanical Mini Type/Hydraulic Precision Type




When placing an order, please indicate the Brand code to get a quicker response.

<p>■ Mechanical Precision Type (Holding Power 100kgf/ Arm Length 345mm)</p> 	<p>ECE-330A</p>  <p>Arm material: aluminium alloy</p>	<p>■ Hydraulic Precision Type (Holding Power 100kgf/ Arm Length 336mm)</p> 	<p>ECE-300A</p>  <p>Arm material: aluminium alloy</p>
<p>■ Mechanical Precision Type (Holding Power 100kgf/ Arm Length 426mm)</p> 	<p>ECE-330AL</p>  <p>Arm material: aluminium alloy</p>	<p>■ Hydraulic Precision Type (Holding Power 100kgf/ Arm Length 434mm)</p> 	<p>ECE-300AL</p>  <p>Arm material: aluminium alloy</p>
<p>■ Mechanical Precision Type (Holding Power 80kgf/Arm Length 345mm)</p> 	<p>ECE-330B</p>  <p>Arm material: aluminium alloy</p>	<p>■ Hydraulic Precision Type (Holding Power 80kgf/ Arm Length 336mm)</p> 	<p>ECE-300B</p>  <p>Arm material: aluminium alloy</p>
<p>■ Mechanical Precision Type (Holding Power 80kgf/Arm Length 278mm)</p> 	<p>ECE-330BS</p>  <p>Arm material: aluminium alloy</p>	<p>■ Hydraulic Precision Type (Holding Power 80kgf/ Arm Length 257mm)</p> 	<p>ECE-300BS</p>  <p>Arm material: aluminium alloy</p>

Part number	Type	Holding power (kgf)	Lower fulcrum bar L1	Upper fulcrum bar (including Inching) L2	Magnetic stand dimensions			Mass (kg)
					L	W	H	
ECE-330A	Mechanical type Precision type	100	175	170	80	50	55	2.0
ECE-330AL		100	210	216	80	50	55	2.2
ECE-330B		80	175	170	60	50	55	1.7
ECE-330BS		80	130	148	60	50	55	1.5
ECE-300A	Hydraulic type Precision type	100	145	191	80	50	55	1.9
ECE-300AL		100	193	241	80	50	55	1.9
ECE-300B		80	145	191	60	50	55	1.6
ECE-300BS		80	103	154	60	50	55	1.4

Ece Tip Detailed Drawing



By adapting hydraulic type, the arm is fixed more security.



Part number
ECE-330AL