


# Phillips Round Flat Head Screws / Ornamental Screws / Washers for Ornamental Screw

## Phillips Round Flat Head Screws



RoHS 10

Type	Material	Surface Treatment
MSARA	SWCH Equivalent	Trivalent Chromate
MSARAS	SUS304 Equivalent	-



MxP (Coarse)	A	(f)	E	Phillips No.
3x0.5	6	0.7	1.75	2
4x0.7	8	0.9	2.3	2
5x0.8	10	1.2	2.8	2
6x1.0	12	1.4	3.4	3

## MSARA (Trivalent Chromate)

Part Number	Unit Price	Volume Discount Rate				
		Type	M - L	1 ~ 29 pc(s)	30 ~ 99 pcs	100 ~ 299 pcs
MSARA	3 - 5	6				
		8				
		10				
		12				
	4 - 6	8				
		10				
		12				
		15				
	5 - 8	10				
		12				
		15				
		20				
6 - 10	12					
	15					
	15					
	20					

## MSARAS (Stainless Steel)

Part Number	Unit Price	Volume Discount Rate				
		Type	M - L	1 ~ 29 pc(s)	30 ~ 99 pcs	100 ~ 299 pcs
MSARAS	3 - 5	6				
		8				
		10				
		12				
	4 - 6	8				
		10				
		12				
		15				
	5 - 8	10				
		12				
		15				
		20				
6 - 10	12					
	15					
	15					
	20					



Ordering Example

Part Number  
MSARAS4-8



## Ornamental Screws Washers for Ornamental Screw



RoHS 10

VIS (Brass)  
VISS (Stainless Steel)

VISZ (Brass)  
VIZS (Stainless Steel)



Type	Material	Surface Treatment
VIS	C2700W	Nickel Plating
VISS	SUS304 Equivalent	-
VISZ	C2700W	Nickel Plating
VIZS	SUS303	-

M (Coarse)	P (Pitch)	D
3	0.5	6
4	0.7	8
5	0.8	10
6	1.0	12

## Ornamental Screws

Part Number	Unit Price	Volume Discount Rate		
		Type	M-L	1 - 99 pc(s)
VIS (Brass)	3-10	15		
		20		
		25		
		30		
		35		
		40		
		45		
		50		
	4-10	15		
		20		
		30		
		35		
		40		
		45		
		45		
		50		

Part Number	Unit Price	Volume Discount Rate		
		Type	M-L	1 - 99 pc(s)
VIS (Brass)	5-10	15		
		20		
		25		
		30		
		35		
		40		
		45		
		50		
	6-10	15		
		20		
		25		
		30		
		35		
		40		
		45		
		50		

Part Number	Unit Price	Volume Discount Rate		
		Type	M-L	1 - 99 pc(s)
VISS (Stainless Steel)	3-10	15		
		20		
		25		
		30		
		35		
		40		
		45		
		50		
	4-10	15		
		20		
		25		
		30		
	5-10	15		
		20		
		25		
		30		
6-10	15			
	20			
	25			
	30			

## Washers for Ornamental Screw

Part Number	Unit Price	Volume Discount Rate		* Quantity			
		Type	d		D	t	* Less than
VISZ (Brass)		3	10	2			2500
		4	12	2.5			1400
		5	14	3			800
		6	16	3.5			500
VIZS (Stainless Steel)		3	10	2			500
		4	12	2.5			400
		5	14	3			300
		6	16	3.5			200



Ordering Example

Part Number  
VIS5-30  
VISZ4