

The number next to the logo mark indicates items in stock for each brand.

Door Closers

Door Stoppers

Hinges

Slide Bolt Latches

Catches

Handles

Keys

Chains

Wire Ropes

Metal Fittings for Handling

Suspension Metal Fittings

Shelf Peg Metal Fittings

Joint Fittings

Steel Wires

Wire Nets

Inspection Doors, Air Inlet/Outlets

Handrails, Slopes

Corrugated Plates

Plastic Materials

Metal Materials

Construction Materials

Sash Rollers

Door Hangers

TRUSCO

TRUSCO

Stock 38,650 Items

## Trigger Snap

RoHS

Com.eco  
Chemical Content Inspection  
Com Drawing




TT-1

- Features**
- Since the eye part rotates, it is used for untwisting a chain, etc.
  - With the spring hook, it can easily open/close.
  - Large opening type.
- Use**
- Suitable for connection of chain/wire/rope, etc., and joint of terminal metal fittings.
- Materials**
- **Stainless Steel (SUS304)**
- Origin**
- China



Example



Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	L (mm)	W1 (mm)	W2 (mm)	S (mm)	H (mm)	d (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
328-6096	TT-0	¥1,148	¥1,240	2.5	48	17	7.5	10	7	11	0.39	20	20
328-6100	TT-1	¥1,306	¥1,410	4.5	60	21	9.5	12	9	13	0.49	20	42
328-6118	TT-2	¥1,805	¥1,950	5.5	78	26	10.5	17	14	20	0.78	20	73

Contact us: 0120-509-849 <http://www.orange-book.com/>

RoHS

NISSA CHAIN

NISSA


Stock 321 Items

## Trigger Snap

- Features**
- A snap with large opening.
- Use**
- For a tip bracket/a hook of chains.
  - For tip brackets of chains for a fence.
- Materials**
- **Zinc die casting (ZDC1)**
  - **Nickel**
- Origin**
- China



P-641



Order Unit: 1 Piece

NISSA CHAIN Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	A (mm)	B (mm)	C (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
405-6914	P-642	¥302	¥280	49	7	16.0	0.04	5	24
405-6906	P-641	¥626	¥580	64	8	16.0	0.07	5	45

Contact us: 06-6722-8221 <http://www.nissa.co.jp/>

MIZUMOTO MACHINE

MM

Stock 529 Items

## Swivel Eye Bolt Snap


RoHS

Com.eco  
Chemical Content Inspection



B-125

- Features**
- Since the eye part rotates, it doesn't tangle when connecting.
  - Since it opens with one touch, it can joint easily.
- Use**
- As a connecting fitting for a chain/a wire rope.
- Materials**
- **Stainless Steel (SUS304)**
- Origin**
- China



Order Unit: 1 Piece

(Price revision date: Jan, 2016) MIZUMOTO MACHINE MFG.Co.Ltd

Order Code	Item No.	Price (per piece)	MSRP (per piece)	D (mm)	L (mm)	W (mm)	S (mm)	H (mm)	d (mm)	t (mm)	Working Load (kN)	SPQ (piece)	Weight (g)
293-1991	B-125	¥1,324	¥1,560	3.0	64	17	6	9	10	4.0	0.20	20	22
293-2008	B-126	¥1,408	¥1,660	4.0	79	20	7	13	14	5.0	0.29	20	33
293-2016	B-127	¥1,469	¥1,730	4.4	91	24	8	15	16	7.0	0.39	20	51
293-2024	B-128	¥2,070	¥2,440	7.0	123	32	13	28	35	7.5	0.49	10	123

Contact us: 079-246-2501 <http://www.mizumoto-mm.co.jp/>

TRUSCO

TRUSCO

Stock 38,650 Items

## Mini Clip (with double link)


RoHS

Com.eco  
Chemical Content Inspection  
Com Drawing



TMPW-0

- Features**
- Since there is a double link, it is easy to attach to a closed object.
- Use**
- For supportive brackets of fall prevention such as industrial machines, tools, etc.
- Materials**
- **Stainless Steel (SUS316)**
- Origin**
- China



Order Unit: 1 Bag

(Price revision date: Jan, 2017) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	D (mm)	L (mm)	W (mm)	S (mm)	R (mm)	L2 (mm)	d (mm)	t (mm)	Working Load (kN)	Q'ty Per Bag (piece)	SPQ (bag)	Weight (g/bag)
300-8746	TMPW-0	¥565	¥610	1.0	15	7.5	3	2.5	12	2.5	1.8	0.01	2	20	2
300-8754	TMPW-1	¥588	¥635	1.0	20	10.0	4	3.5	15	3.5	2.4	0.01	2	20	4
300-8762	TMPW-2	¥685	¥740	1.2	26	12.0	5	4.0	18	4.2	3.0	0.01	2	20	8
300-8771	TMPW-3	¥990	¥1,070	1.4	34	15.0	6	5.0	22	6.0	4.3	0.01	2	20	16

Contact us: 0120-509-849 <http://www.orange-book.com/>