


Prices displayed include 8% tax.

KURITA **Stock 47 Items** **"Cyclone Nozzle"** RoHS 栗田製作所


KURITA **Stock 47 Items** **Stainless Steel Long Nozzle** RoHS 栗田製作所



N-AG90DN



- Features**
- It is a power injection nozzle of a shock with continuous ejection.
 - By the effect of intermittent wave, water, etc. accumulated in the dent is ejected.
- Origin**
- Japan



SUS-AG45-300

- Features**
- Long nozzle made of stainless steel with excellent corrosion resistance.
 - The tip is drawn so that there is no worry of falling parts.
- Origin**
- Japan

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nozzle Length (mm)	Nozzle Opening Diameter (mm)	Nozzle Mounting Port	SPQ (piece)	Weight (g)
818-9241	N-AG90DN	¥4,798	¥4,785	54.5	2.5	G1/8	1	39

Contact us:03-5638-8261 <http://www.cup-kurita.co.jp/>

Order Unit: 1 Piece


Order Code	Item No.	Price (per piece)	MSRP (per piece)	Nozzle Length (mm)	Nozzle Opening Diameter (mm)	Nozzle Mounting Port	Weight (g)
818-9243	SUS-AG45-150	¥10,902	¥10,870	150	2.3	G1/8	24
818-9244	SUS-AG45-300	¥14,171	¥14,130	300	2.3	G1/8	39

Contact us:03-5638-8261 <http://www.cup-kurita.co.jp/>

TRUSCO **Stock 38,650 Items** **Bounce-Back Prevention Panel for Air Duster** RoHS



- Use Specs Origin**
- Preventing split of dust, cutting fluid etc during dust work.
 - Can be mounted on a nozzle air duster of outer diameter 7mm or 5mm
 - Japan



TD-HB7

Item No.	Compatible Model
TD-HB5	TD-100-1, TD-60-1R
TD-HB5-150	
TD-HB5-200	
TD-HB7	TD-10-1, TD-18-1N, TD-30-1, TD-70-1, TD-80-1
TD-HB7-150	
TD-HB7-200	



- Warning**
- When using, please use with protective equipment such as safety glasses.

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Diameter (mm)	Thickness (board) (mm)	Center Hole Diameter (mm)	SPQ (piece)	Weight (g)
336-2621	TD-HB5	¥ 694	¥ 750	100	2	4.75	10	10
374-6399	TD-HB5-150	¥1,351	¥1,460	150	2	4.75	10	38
374-6411	TD-HB5-200	¥1,574	¥1,700	200	2	4.75	10	66
336-2612	TD-HB7	¥ 694	¥ 750	100	2	6.75	10	10
374-6402	TD-HB7-150	¥1,351	¥1,460	150	2	6.75	10	38
374-6429	TD-HB7-200	¥1,574	¥1,700	200	2	6.75	10	66

Contact us:0120-509-849 <http://www.orange-book.com/>


TRUSCO **Stock 38,650 Items** **Mini Air Filter for Air Duster**



- Features**
- Easily remove moisture and oil, etc. in the air hose at hands.
 - Material of body is made of polycarbonate.
 - Equipped with the push valve for draining.
 - It is possible to check accumulation of water and drain.
- Specs**
- Max Working Pressure: 0.7MPa
 - Filtration Precision :40 μ
- Origin**
- China



TD-MF



Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Total Length (mm)	Connection Port Diameter	SPQ (piece)	Weight (g)
282-5473	TD-MF	¥2,823	¥3,050	87	G1/4	20	99

Contact us:0120-509-849 <http://www.orange-book.com/>

Pneumatic Tools

Air Impact Wrenches

Air Ratchet Wrenches

Air Screwdrivers

Air Drills

Air Micro Grinders

Air Grinders

Air Files

Air Sanders

Air Belt Sanders

Air Chisels

Air Hammers

Air Saws

Air Bevelers

Air Nippers

Air Dusters

Air Guns

Air Blast Machines